

# CA-12S2S8A80DN - Cable connector



1621436

<https://www.phoenixcontact.com/us/products/1621436>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the product with assembled crimp contacts. Please order crimp contacts separately.

M23, Cable connector, application: Signal, series: CA, straight, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Counter direction, contact connection type: Socket, Crimp connection, cable diameter range: 3 mm ... 14.5 mm, coding: S. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Commercial data

Item number	1621436
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAEA
GTIN	4046356932530
Weight per piece (including packing)	93.5 g
Weight per piece (excluding packing)	86.89 g
Customs tariff number	85366990
Country of origin	DE

# CA-12S2S8A80DN - Cable connector



1621436

<https://www.phoenixcontact.com/us/products/1621436>

## Technical data

### Notes

Order information:	Order crimp contacts separately
Order information:	When using a specific cable with $\varnothing$ 3 mm ... 4 mm, it may be necessary to use the special cable seal (1786601)

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Coding	S
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	12
Direction of rotation	Counter direction
Connection profile	12
Number (Contact group 1)	12
Contact diameter (Contact group 1)	1 mm
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Material for screw connection	CuZn
Degree of protection (plugged in)	IP67

#### Seal

External cable diameter	3 mm ... 14.5 mm
Seal material	NBR

# CA-12S2S8A80DN - Cable connector




1621436

<https://www.phoenixcontact.com/us/products/1621436>

## Drawings

Schematic diagram



Contact chamber numbering (view of plug-in side), socket counter direction

# CA-12S2S8A80DN - Cable connector



1621436

<https://www.phoenixcontact.com/us/products/1621436>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 10.0	EC002635
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CA-12S2S8A80DN - Cable connector



1621436

<https://www.phoenixcontact.com/us/products/1621436>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	84d39dd8-2f02-4d36-b38b-3cbafa618ddc

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)