

RC-17S1N12YF00 - Device connector front mounting with knurled nut



1624882

<https://www.phoenixcontact.com/us/products/1624882>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting with knurled nut, application: Signal, series: RC, straight, shielded: no, Screw locking mechanism, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Socket, Solder cup, Axial O-ring, 4x Ø 3.2, coding: N

Commercial data

Item number	1624882
Packing unit	40 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFO
GTIN	4046356748865
Weight per piece (including packing)	53 g
Weight per piece (excluding packing)	53 g
Country of origin	DE

RC-17S1N12YF00 - Device connector front mounting with knurled nut



1624882

<https://www.phoenixcontact.com/us/products/1624882>

Technical data

Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	17
Direction of rotation	Standard
Connection profile	17
Number (Contact group 1)	17
Contact diameter (Contact group 1)	1 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm ²
Litz wires Max. cross section (Contact group 1)	1 mm ²
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Order information:	Order contact inserts separately
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	none
Housing material	Metal
Degree of protection (plugged in)	IP67
Seal for the device	Axial O-ring


RC-17S1N12YF00 - Device connector front mounting with knurled nut

1624882

<https://www.phoenixcontact.com/us/products/1624882>

Drawings

Schematic diagram




Connector pin assignment

RC-17S1N12YF00 - Device connector front mounting with knurled nut

1624882

<https://www.phoenixcontact.com/us/products/1624882>

Schematic diagram



Dimensional drawing

RC-17S1N12YF00 - Device connector front mounting with knurled nut



1624882

<https://www.phoenixcontact.com/us/products/1624882>

Classifications

UNSPSC

UNSPSC 21.0	39131505
-------------	----------

RC-17S1N12YF00 - Device connector front mounting with knurled nut



1624882

<https://www.phoenixcontact.com/us/products/1624882>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com