

EV-TBG3JC-1AC32A-5,0M6,0ESBK01 - AC charging cable



1627688

<https://www.phoenixcontact.com/us/products/1627688>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect, Type 2, GB/T, Mobile AC charging cable, with vehicle charging connector and infrastructure charging plug, cable: 5 m, black, straight, with protective cap, with locking option for padlock, housing: black, gray, PHOENIX CONTACT logo, IEC 62196-2, GB/T 20234.2-2015, for charging electric vehicles (EV) with alternating current (AC) via type 2 vehicle charging inlets

Product description

Mobile AC charging cable with vehicle charging connector and infrastructure charging plug for charging electric vehicles (EV) with alternating current (AC) via type 2 vehicle charging inlets, compatible with GB/T infrastructure charging sockets at charging stations for e-mobility (EVSE)

Your advantages

- Complete product range
- Convenient handling due to the ergonomic, triple award-winning design
- Available with your logo on request - for consistent branding of your charging station
- Longitudinal water tightness reliably prevents water ingress
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- Tested in accordance with automotive standards LV124, LV214, and LV215-2
- Tested in accordance with EV Ready 37 requirements

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1627688 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | XWBAEH |
| GTIN | 4055626357454 |
| Weight per piece (including packing) | 2,573 g |
| Weight per piece (excluding packing) | 2,573 g |
| Country of origin | DE |

EV-TBG3JC-1AC32A-5,0M6,0ESBK01 - AC charging cable



1627688

<https://www.phoenixcontact.com/us/products/1627688>

Technical data

Product properties

| | |
|-------------------|--|
| Product type | AC charging cable |
| Product family | CHARX connect |
| Type | Mobile AC charging cable with vehicle charging connector and infrastructure charging plug |
| Design | with protective cap with locking option for padlock |
| Charging standard | Type 2 GB/T |
| Charging mode | Mode 3, Case B |
| Affixed logo | PHOENIX CONTACT logo |

Electrical properties

Charging power and current (AC charging, 1-phase)

| | |
|--------------------------|-------------------|
| Type of charging current | AC single-phase |
| Charging current | 32 A AC (1-phase) |
| Charging power | 8 kW |
| Rated voltage | 250 V |

Material specifications

| | |
|------------------------|--------------|
| Color (Housing) | black (9005) |
| Color (Handle area) | gray (7042) |
| Color (Mating face) | black (9005) |
| Color (Protective cap) | black (9005) |
| Color (Cable) | black (9005) |

Cable/line

| | |
|--------------------------------|---|
| Cable length | 5 m |
| Wiring standards/regulations | prEN 50620/DIN EN 50620 |
| Wiring certifications | VDE |
| Cable weight | max. 305.00 kg/km |
| Cable type | Class 5 |
| Cable type | straight |
| Cable structure | 3 x 6.0 mm ² + 1 x 0.5 mm ² |
| External cable diameter | 12.80 mm ±0.4 mm |
| Outer sheath, material | TPE-U |
| Stripping length of the sheath | 60 mm ±15 mm |
| Stripping length | 60 mm ±15 mm |
| Cable resistance | ≤ 0.0033 Ω/m (based on a power core, at an ambient temperature of 20°C) |
| Bending radius | min. 96 mm (7.5x diameter) |

EV-TBG3JC-1AC32A-5,0M6,0ESBK01 - AC charging cable



1627688

<https://www.phoenixcontact.com/us/products/1627688>

| | |
|------------------------------|---|
| Cable length | 5 m |
| Stripping length | 60 mm ±15 mm |
| External cable diameter | 12.80 mm ±0.4 mm |
| Cable type | Class 5 |
| Wiring certifications | VDE |
| Wiring standards/regulations | prEN 50620/DIN EN 50620 |
| Cable resistance | ≤ 0.0033 Ω/m (based on a power core, at an ambient temperature of 20°C) |

Standards and regulations

Standards

| | |
|-----------------------|-------------------|
| Standards/regulations | IEC 62196-2 |
| | GB/T 20234.2-2015 |

EV-TBG3JC-1AC32A-5,0M6,0ESBK01 - AC charging cable




1627688

<https://www.phoenixcontact.com/us/products/1627688>


Drawings

Dimensional drawing



Vehicle connector

Dimensional drawing




Infrastructure plug

EV-TBG3JC-1AC32A-5,0M6,0ESBK01 - AC charging cable

1627688

<https://www.phoenixcontact.com/us/products/1627688>

Connection diagram






Pin assignment of Infrastructure Plug

EV-TBG3JC-1AC32A-5,0M6,0ESBK01 - AC charging cable

1627688

<https://www.phoenixcontact.com/us/products/1627688>

Schematic diagram




Operating instructions

EV-TBG3JC-1AC32A-5,0M6,0ESBK01 - AC charging cable

1627688

<https://www.phoenixcontact.com/us/products/1627688>

Schematic diagram



Pin assignment of the Vehicle Connector

EV-TBG3JC-1AC32A-5,0M6,0ESBK01 - AC charging cable



1627688

<https://www.phoenixcontact.com/us/products/1627688>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121500 |
|-------------|----------|

EV-TBG3JC-1AC32A-5,0M6,0ESBK01 - AC charging cable



1627688

<https://www.phoenixcontact.com/us/products/1627688>

Environmental product compliance

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-10 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
|--|--|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com