

EV-CC-AC1-M3-CBC-SER-PCB - AC charging controller



1622453

<https://www.phoenixcontact.com/us/products/1622453>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The EV-CC-AC1-M3-CBC-SER-PCB charging controller as PCB is used for charging electric vehicles at 3-phase AC networks according to IEC 61851-1, Mode 3. All charging functions, comprehensive configuration settings as well as a locking controller are already integrated.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1622453 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | XWBRAA |
| GTIN | 4055626039770 |
| Weight per piece (including packing) | 293 g |
| Weight per piece (excluding packing) | 293 g |
| Country of origin | DE |

EV-CC-AC1-M3-CBC-SER-PCB - AC charging controller



1622453

<https://www.phoenixcontact.com/us/products/1622453>

Technical data

Product properties

| | |
|---------------------------------|------------------------|
| Product type | AC charging controller |
| Product family | CHARX control basic |
| Charging mode | Mode 3, Case B + C |
| Operating mode | Stand-Alone |
| | Client |
| Modem for communication present | no |
| Number of charging points | 1 |

Electrical properties

| | |
|--------------------------|----|
| Type of charging current | AC |
|--------------------------|----|

Input data

Digital

| | |
|-----------------------------|-------------------|
| Number of digital inputs | 5 |
| Frequency range | 50 Hz ... 60 Hz |
| Nominal power consumption | < 0.5 W (No-load) |
| Nominal current I_N | ≤ 1 mA |
| Nominal input voltage U_N | 12 V |
| Input voltage range U1 | 0 V ... 3 V (Off) |
| Input voltage range U2 | 9 V ... 15 V (On) |

Output data

Digital

| | |
|------------------------|--|
| Output name | 4 digital outputs |
| Connection technology | Screw connection |
| Maximum output voltage | 30 V |
| Maximum output current | 0.5 A (Total current for all outputs; internally supplied) |
| | 0.6 A (Per output; externally supplied) |

Switching

| | |
|---------------------------|-------------------------------|
| Output name | Relay output C _{1,2} |
| Minimum switching power | 1500 VA |
| Maximum switching voltage | 250 V AC (External supply) |
| Max. switching current | 6 A |

Switching

| | |
|---------------------------|------------------------|
| Output name | Relay output LO+/- |
| Minimum switching power | 24 VA |
| Maximum switching voltage | 12 V (Internal supply) |
| Max. switching current | 2 A |

EV-CC-AC1-M3-CBC-SER-PCB - AC charging controller



1622453

<https://www.phoenixcontact.com/us/products/1622453>

Connection data

| | |
|----------------------------------|---|
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Interfaces

| | |
|-----------|--------|
| Interface | RS-485 |
|-----------|--------|

RS-485

| | |
|--------------------------|-------------------------------------|
| Interface | RS-485 2-wire |
| Bus system | RS-485 |
| Connection method | Screw connection |
| Number of interfaces | 1 |
| Transmission speed range | 9.6 kbps ... 19.2 kbps (adjustable) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -35 °C ... 70 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Permissible humidity (operation) | 30 % ... 95 % |

Standards and regulations

Standards

| | |
|-----------------------|-------------|
| Standards/regulations | IEC 61851-1 |
|-----------------------|-------------|

Mounting

| | |
|-------------------|--------------|
| Mounting type | PCB mounting |
| Mounting position | any |

EV-CC-AC1-M3-CBC-SER-PCB - AC charging controller



1622453

<https://www.phoenixcontact.com/us/products/1622453>

Classifications

ECLASS

ECLASS-13.0

27144703

ETIM

ETIM 9.0

EC002889

UNSPSC

UNSPSC 21.0

39121800

EV-CC-AC1-M3-CBC-SER-PCB - AC charging controller



1622453

<https://www.phoenixcontact.com/us/products/1622453>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-10 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| | 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7) |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com