

EV-T2M3PC-3AC20A-12M2,5ESBK00 - AC charging cable



1622581

<https://www.phoenixcontact.com/us/products/1622581>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CHARX connect, Type 2, cable: 12 m, IEC 62196-2, Mobile AC charging cable with vehicle connector and infrastructure plug, with protective cap, NOTE: The capacitance between CP and PE exceeds the normative guideline value of 1500 pF.



Product description

Mobile AC charging cable with vehicle charging connector and infrastructure charging plug for charging electric vehicles (EV) with alternating current (AC) via type 2 vehicle charging inlets, compatible with type 2 infrastructure charging sockets at charging stations for e-mobility (EVSE)

Your advantages

- Consistent design of all Phoenix Contact Vehicle Connectors and Infrastructure Plugs
- Silver-plated surface of the power and signal contacts
- Developed and produced in accordance with the IATF 16949 automotive standard and ISO 9001
- Convenient handling, thanks to the ergonomic handle and additional, rubber grip components

Commercial data

Item number	1622581
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	XWBAEC
GTIN	4055626046426
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

EV-T2M3PC-3AC20A-12M2,5ESBK00 - AC charging cable



1622581

<https://www.phoenixcontact.com/us/products/1622581>

Technical data

Notes

General	NOTE: The capacitance between CP and PE exceeds the normative guideline value of 1500 pF.
General	Signal transmission may be adversely affected (IEC 61851-1, Annex A, Table A.2, Note c).
General	Interference-free V2G communication in accordance with ISO 15118 is not guaranteed for cable lengths over 10 m (ISO IEC 15118-3, A.11.3, Table A.11).
General	Cable management is required in certain regions if the cable length exceeds 5.0 m (Switzerland) or 7.5 m (USA) (IEC 61851-1).

Product properties

Product type	AC charging cable
Product family	CHARX connect
Charging standard	Type 2
Charging mode	Mode 3, Case B

Electrical properties

Charging power and current (AC charging, 3-phase)

Type of charging current	AC 3-phase
Charging current	20 A AC (1-phase)
Charging power	16.63 kW
Rated voltage	440 V

Cable/line

Cable length	12 m
--------------	------

Standards and regulations

Standards

Standards/regulations	IEC 62196-2
-----------------------	-------------

EV-T2M3PC-3AC20A-12M2,5ESBK00 - AC charging cable



1622581

<https://www.phoenixcontact.com/us/products/1622581>

Drawings

Dimensional drawing



Vehicle connector

Dimensional drawing




Infrastructure plug

EV-T2M3PC-3AC20A-12M2,5ESBK00 - AC charging cable

1622581

<https://www.phoenixcontact.com/us/products/1622581>

Connection diagram




Pin assignment of Infrastructure Plug

EV-T2M3PC-3AC20A-12M2,5ESBK00 - AC charging cable

1622581

<https://www.phoenixcontact.com/us/products/1622581>

Schematic diagram



Operating instructions

EV-T2M3PC-3AC20A-12M2,5ESBK00 - AC charging cable

1622581

<https://www.phoenixcontact.com/us/products/1622581>

Schematic diagram



Pin assignment of the Vehicle Connector

EV-T2M3PC-3AC20A-12M2,5ESBK00 - AC charging cable



1622581

<https://www.phoenixcontact.com/us/products/1622581>

Classifications

UNSPSC

UNSPSC 21.0

39121522

EV-T2M3PC-3AC20A-12M2,5ESBK00 - AC charging cable



1622581

<https://www.phoenixcontact.com/us/products/1622581>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com