

# HC-26P1N8A4300 - Device connector rear mounting



1623262

<https://www.phoenixcontact.com/us/products/1623262>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 28-pos.  
product version

Device connector rear mounting, application: Signal, straight, Screw locking mechanism, M27, number of positions: 26, contact connection type: Pin, Radial O-ring, shielded: yes, number of positions: 26, connection method: Crimp connection, series: HC, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

## Commercial data

Item number	1623262
Packing unit	24 pc
Minimum order quantity	1 pc
Product key	ABRAJR
GTIN	4055626270142
Weight per piece (including packing)	39.2 g
Weight per piece (excluding packing)	35.42 g
Country of origin	DE

# HC-26P1N8A4300 - Device connector rear mounting



1623262

<https://www.phoenixcontact.com/us/products/1623262>

## Technical data

### Notes

Order information:	Order crimp contacts Ø 1 mm separately
--------------------	--

### Mounting

Mounting type	Rear mounting/square flange (4x M3)
---------------	-------------------------------------

### Product properties

Product type	Circular connectors (device side)
Series	HC
Application	Signal
Number of positions	26
Connection profile	26
Shielded	yes
Coding	N
Thread type	M27

### Material specifications

Flammability rating according to UL 94	V0
Seal material	FPM or NBR or EPDM

### Electrical properties

#### Contact

Contact diameter	1 mm
Nominal current $I_N$	8 A
Nominal voltage $U_N$	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

### Connection data

#### Conductor connection

Connection method	Crimp connection
Contact connection type	Pin

### Connector

Type	straight
Direction of rotation	Standard

### Environmental and real-life conditions

#### Ambient conditions

# HC-26P1N8A4300 - Device connector rear mounting



1623262

<https://www.phoenixcontact.com/us/products/1623262>

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

# HC-26P1N8A4300 - Device connector rear mounting




1623262

<https://www.phoenixcontact.com/us/products/1623262>


## Drawings

Dimensional drawing



Installation dimensions

Schematic diagram



Connector pin assignment

# HC-26P1N8A4300 - Device connector rear mounting



1623262

<https://www.phoenixcontact.com/us/products/1623262>

## Classifications

### ECLASS

ECLASS-13.0	27440109
ECLASS-15.0	27440109

### ETIM

ETIM 10.0	EC003569
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# HC-26P1N8A4300 - Device connector rear mounting



1623262

<https://www.phoenixcontact.com/us/products/1623262>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	e7517bee-2bbc-409d-8be9-67e3a02f388d

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)