SB-Z0016 - Crimping pliers

1624515

https://www.phoenixcontact.com/us/products/1624515

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The illustration can vary depends on the configuration

Manual crimping pliers for turned crimp contacts Ø 3.6 mm, litz wire cross section of 10 mm^2 ... 16 mm^2 without locator for axial stop

Commercial data

Item number	1624515
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB36
Product key	ABRFAA
GTIN	4055626280387
Weight per piece (including packing)	1,014.2 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	82032000
Country of origin	DE

Technical data

Product properties

Product type	Crimping tool

Crimping position 1

Min. cross section	16 mm²

Crimping position 2

Max. cross section	10 mm²

Connection data

Conductor connection

Cross section range, metric	10 mm² ... 16 mm²

Dimensions

Length	210 mm

Material specifications

Flammability rating according to UL 94	V0

Classifications

UNSPSC

UNSPSC 21.0	39121413

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com