

RC-09S2N121600 - Cable connector



1624802

<https://www.phoenixcontact.com/us/products/1624802>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: RC, straight, shielded: no, Screw locking mechanism, No. of pos.: 8+1, Direction of rotation: Counter direction, contact connection type: Socket, Solder cup, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1245267

The figure shows the 12-pos. product version with standard contact chamber numbering

Commercial data

Item number	1624802
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAFA
GTIN	4046356920186
Weight per piece (including packing)	81.95 g
Weight per piece (excluding packing)	78.36 g
Country of origin	DE

RC-09S2N121600 - Cable connector



1624802

<https://www.phoenixcontact.com/us/products/1624802>

Technical data

Product properties

Product type	Circular connector (cable-side)
Thread type	M23

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Socket
Application	Signal
Number of positions	9
Direction of rotation	Counter direction
Connection profile	8+1
Number (Contact group 1)	1
Contact diameter (Contact group 1)	2 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm ²
Litz wires Max. cross section (Contact group 1)	2.5 mm ²
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	8
Contact diameter (Contact group 2)	1 mm
Litz wires Max. cross section (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A
Rated voltage Contact (Contact group 2)	48 V AC 48 V AC

Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Screw locking mechanism
Pg screw connection	Pg11
Mounting type	Screw mounting (Pg11)

RC-09S2N121600 - Cable connector



1624802

<https://www.phoenixcontact.com/us/products/1624802>

Material (Housing)	Metal
Degree of protection (plugged in)	IP65
	IP67

RC-09S2N121600 - Cable connector




1624802

<https://www.phoenixcontact.com/us/products/1624802>

Drawings

Schematic diagram



Connector pin assignment

RC-09S2N121600 - Cable connector



1624802

<https://www.phoenixcontact.com/us/products/1624802>

Schematic diagram



Dimensional drawing

RC-09S2N121600 - Cable connector



1624802

<https://www.phoenixcontact.com/us/products/1624802>

Classifications

ECLASS

ECLASS-13.0

27371392

ETIM

ETIM 9.0

EC002498

UNSPSC

UNSPSC 21.0

39121100

RC-09S2N121600 - Cable connector



1624802

<https://www.phoenixcontact.com/us/products/1624802>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b56d1096-271d-4f5e-aea8-04e01a4ddafc

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com