

RF-17P1N8A80DUS - Cable connector



1625228

<https://www.phoenixcontact.com/us/products/1625228>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1245301

Commercial data

Item number	1625228
Packing unit	20 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ABRAGA
GTIN	4046356877398
Weight per piece (including packing)	94.4 g
Weight per piece (excluding packing)	94.4 g
Country of origin	DE

RF-17P1N8A80DUS - Cable connector



1625228

<https://www.phoenixcontact.com/us/products/1625228>

Technical data

Notes

Order information:

Order crimp contacts Ø 1 mm separately

Product properties

Product type

Circular connector (cable-side)

Material specifications

Flammability rating according to UL 94

V0

RF-17P1N8A80DUS - Cable connector



1625228

<https://www.phoenixcontact.com/us/products/1625228>

Classifications

ECLASS

ECLASS-13.0	27440116
-------------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RF-17P1N8A80DUS - Cable connector



1625228

<https://www.phoenixcontact.com/us/products/1625228>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	55724ae9-6da8-447f-b37c-52200da278ea

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com