

# RC-06S1NS24100 - Device connector rear mounting



1625929

<https://www.phoenixcontact.com/us/products/1625929>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector rear mounting, application: Signal, series: RC, straight, Screw locking mechanism, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Socket, Screw connection, Flat gasket, Panel thickness min.: 2.7 mm, Panel thickness max.: 3.5 mm, coding: N

The figure shows the 12-pos. product version

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1625929                        |
| Packing unit                         | 40 pc                          |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | ABRAFR                         |
| GTIN                                 | 4046356982658                  |
| Weight per piece (including packing) | 30.43 g                        |
| Weight per piece (excluding packing) | 30.43 g                        |
| Country of origin                    | DE                             |

# RC-06S1NS24100 - Device connector rear mounting



1625929

<https://www.phoenixcontact.com/us/products/1625929>

## Technical data

### Product properties

|              |                                   |
|--------------|-----------------------------------|
| Product type | Circular connectors (device side) |
|--------------|-----------------------------------|

### Connector

#### Insulating body

|   |  |
|---|--|
| Coding  | N  |
| Material (Insulating body)                      | PBT                                      |
| Material (Contact)                              | CuZn                                     |
| Material (Contact surface)                      | Ni/Au                                    |
| Insertion/withdrawal cycles                     | 50                                       |
| Connection method                               | Screw connection                         |
| Contact switching type                          | Socket                                   |
| Application                                     | Signal                                   |
| Number of positions                             | 6  |
| Direction of rotation                           | Standard                                 |
| Connection profile                              | 6  |
| Number (Contact group 1)                        | 6  |
| Contact diameter (Contact group 1)              | 2 mm                                     |
| Litz wires Min. cross section (Contact group 1) | 0.08 mm <sup>2</sup>                     |
| Litz wires Max. cross section (Contact group 1) | 1 mm <sup>2</sup>                        |
| Rated current Contact (Contact group 1)         | 20 A (for max. connection cross section) |
| Rated voltage Contact (Contact group 1)         | 48 V AC<br>74 V DC                       |
| Rated surge voltage                             | 1.5 kV                                   |
| Overvoltage category                            | III                                      |
| Degree of pollution                             | 3  |

#### Housing


|                                   |                                     |
|-----------------------------------|-------------------------------------|
| Type                              | Flange housing                      |
| Thread type                       | M23                                 |
| Design                            | straight                            |
| Type of locking                   | Screw locking mechanism             |
| Pg screw connection               | none                                |
| Mounting type                     | Rear mounting/square flange (4x M3) |
| Material (Housing)                | Metal                               |
| Degree of protection (plugged in) | IP67                                |
| Seal for the device               | Flat gasket                         |

# RC-06S1NS24100 - Device connector rear mounting


1625929

<https://www.phoenixcontact.com/us/products/1625929>

## Drawings



Dimensional drawing




Installation dimensions

# RC-06S1NS24100 - Device connector rear mounting

1625929

<https://www.phoenixcontact.com/us/products/1625929>



Dimensional drawing



Installation dimensions

# RC-06S1NS24100 - Device connector rear mounting



1625929

<https://www.phoenixcontact.com/us/products/1625929>

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)