

ME-IO-S 55 CPU 100 7035 - Electronics housing



1632614

<https://www.phoenixcontact.com/us/products/1632614>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, CPU housing, with vents, width: 53 mm, height: 100 mm, depth: 80 mm, color: light gray (similar RAL 7035), cross connection: Bus connector (optional), number of positions cross connector: 8

Your advantages

- Simple module assembly with 2 side panels, 1 center element, and 2 DIN rail fixing levers
- High connection density with 18-pos. connector with 5 mm pitch
- Ideal for price-sensitive applications thanks to the simple design and predefined module layout
- Machinable flaps in the CPU module allow application-specific customization
- Easy cabling in the module thanks to pre-printed 18-pos. front connector
- Features a space-saving status indicator

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1632614 |
| Packing unit | 30 pc |
| Minimum order quantity | 30 pc |
| Sales key | AC15 |
| Product key | ACHEBF |
| GTIN | 4067923152823 |
| Weight per piece (including packing) | 75 g |
| Weight per piece (excluding packing) | 68 g |
| Customs tariff number | 85389099 |
| Country of origin | CN |

Technical data

Notes

| | |
|----------------|---|
| Recommendation | Further information and detailed dimensions are available in the download area. |
|----------------|---|

Product properties

| | |
|------------------------------|--------------------------|
| Product type | Complete housing |
| Housing type | DIN rail housing |
| Housing type | Multifunctional housings |
| Housing series | ME-IO-S |
| Product family | ME-IO-S.. |
| Ventilation openings present | yes |

Dimensions

| | |
|--------|--------|
| Width | 53 mm |
| Height | 100 mm |
| Depth | 80 mm |

PCB design

| | |
|---------------|---------------------|
| PCB thickness | 1.45 mm ... 1.75 mm |
|---------------|---------------------|

Material specifications

| | |
|--|------------------------|
| Color (Housing) | light gray (RAL 7035) |
| Color (Base latch) | deep orange (RAL 2011) |
| Material Housing | PC |
| Material Base latch | POM |
| Flammability rating according to UL 94 | V0 |
| CTI according to IEC 60112 | 600 |
| Surface characteristics | untreated |

Environmental and real-life conditions

Vibration test

| | |
|------------------------|-----------------------------|
| Specification | IEC 60068-2-6:2007-12 |
| Frequency | 10 - 150 - 10 Hz |
| Sweep speed | 1 octave/min |
| Amplitude | 0.35 mm (10 Hz ... 60.1 Hz) |
| Acceleration | 5g (60.1 Hz ... 150 Hz) |
| Test duration per axis | 2.5 h |
| Test directions | X-, Y- and Z-axis |

Glow-wire test

| | |
|---------------|------------------------|
| Specification | IEC 60695-2-11:2021-10 |
| Temperature | 850 °C |

1632614

<https://www.phoenixcontact.com/us/products/1632614>

| | |
|------------------|------|
| Time of exposure | 30 s |
|------------------|------|

Needle-flame test

| | |
|---------------|------------------------|
| Specification | IEC 60695-11-5:2016-12 |
|---------------|------------------------|

Thermal stability / ball thrust test

| | |
|---------------|------------------------|
| Specification | IEC 60695-10-2:2014-02 |
| Temperature | 125 °C |
| Test duration | 1 h |
| Force | 20 N |

Shocks

| | |
|--------------------------------|-----------------------------------|
| Specification | IEC 60068-2-27 |
| Pulse shape | Semi-sinusoidal |
| Acceleration | 15g |
| Shock duration | 11 ms |
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |

Degree of protection (IP code)

| | |
|---------------|---|
| Specification | IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08 |
|---------------|---|

Ambient conditions

| | |
|---|--|
| Max. IP code to attain | IP20 |
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |

PCB data

| | |
|-----------------------|---------------------|
| Number of PCB holders | 2 |
| Type of PCB mount | Latching |
| Thickness of the PCB | 1.45 mm ... 1.75 mm |

Mounting


| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

Packaging specifications

| | |
|----------------------|---------------------|
| Type of packaging | packed in cardboard |
| Outer packaging type | Carton |

Drawings

Schematic diagram



ME-IO-S 55 CPU 100 7035 - Electronics housing



1632614

<https://www.phoenixcontact.com/us/products/1632614>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1632614>



UL Recognized

Approval ID: E240868

ME-IO-S 55 CPU 100 7035 - Electronics housing



1632614

<https://www.phoenixcontact.com/us/products/1632614>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190101 |
| ECLASS-15.0 | 27190101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001031 |
|-----------|----------|

ME-IO-S 55 CPU 100 7035 - Electronics housing



1632614

<https://www.phoenixcontact.com/us/products/1632614>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com