

1636460

<https://www.phoenixcontact.com/us/products/1636460>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

HEAVYCON contact insert module, female, 6-pos., crimp connection



Commercial data

Item number	1636460
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF62
Product key	AF7ACB
GTIN	4046356028202
Weight per piece (including packing)	11.74 g
Weight per piece (excluding packing)	11.55 g
Customs tariff number	85366990
Country of origin	DE

HC-M-06P-MOD-BU - Contact insert module



1636460

<https://www.phoenixcontact.com/us/products/1636460>

Technical data

Notes

General	For HEAVYCON housing type B6 to B48, HC-M-MHR... hinged retaining frame required, CK2,5-ED... crimp contacts (crimp contacts not supplied as standard)
---------	--

Mounting

Assembly note	Housing height ≥ 52 mm. Plug-in connections may only be operated only when there is no load/voltage.
---------------	--

Product properties

Product type	Modular contact insert
Series	HC-M-06
Application	Power
Number of positions	6
Connection profile	6
Contact numbering	1 - 6
Number of module slots	1
Contact material type	turned

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data


Connection technology

Connection technology	Crimp connection
-----------------------	------------------

Conductor connection

Conductor cross-section	0.5 mm ² ... 4 mm ²
Connection cross section AWG	20 ... 12
Stripping length of the individual wire	7.5 mm

Dimensions

Dimensional drawing	
Width	34.2 mm
Height	37.4 mm
Length	14.6 mm

Mechanical characteristics

HC-M-06P-MOD-BU - Contact insert module



1636460

<https://www.phoenixcontact.com/us/products/1636460>

Minimum housing height	52 mm
Contact diameter	2.5 mm

Electrical properties

Rated voltage (III/3)	830 V
Rated surge voltage	8 kV
Rated current	16 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag (alternatively Au)
Contact carrier material	PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

HC-M-06P-MOD-BU - Contact insert module


1636460

<https://www.phoenixcontact.com/us/products/1636460>



Drawings

Dimensional drawing



Female insert


HC-M-06P-MOD-BU - Contact insert module

1636460

<https://www.phoenixcontact.com/us/products/1636460>




Schematic diagram



Connector pin assignment, connection side

1636460

<https://www.phoenixcontact.com/us/products/1636460>



Derating diagram (6 modules in HC-B 24 housing)

HC-M-06P-MOD-BU - Contact insert module



1636460
<https://www.phoenixcontact.com/us/products/1636460>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com