

SACC-M12MS-4QO-0,34M TURCK - Connector



1642205

<https://www.phoenixcontact.com/us/products/1642205>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, 4-position, Plug straight M12, coding: A, knurl material: Zinc die-cast, nickel-plated, external cable diameter 3.5 mm ... 6 mm, Customer version

Commercial data

Item number	1642205
Packing unit	50 pc
Minimum order quantity	1 pc
Product key	AF2CCA
GTIN	4017918936464
Weight per piece (including packing)	15.35 g
Weight per piece (excluding packing)	8.71 g
Country of origin	DE

SACC-M12MS-4QO-0,34M TURCK - Connector



1642205

<https://www.phoenixcontact.com/us/products/1642205>

Technical data

Notes

Assembly note	NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
---------------	---

Product properties

Product type	Circular connector (cable-side)
Number of positions	4
No. of cable outlets	1
Coding	A
Cable outlet	straight

Dimensions

External dimensions

Outside diameter	3.5 mm ... 6 mm
------------------	-----------------

Material specifications

Material for screw connection	Zinc die-cast, nickel-plated
-------------------------------	------------------------------

Connector

Connection 1

Head design	Plug
Head cable outlet	straight
Head thread type	M12
Coding	A

SACC-M12MS-4QO-0,34M TURCK - Connector



1642205

<https://www.phoenixcontact.com/us/products/1642205>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

UNSPSC

UNSPSC 21.0	39121413
-------------	----------

SACC-M12MS-4QO-0,34M TURCK - Connector



1642205

<https://www.phoenixcontact.com/us/products/1642205>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com