

CA-19S1NP2HZ00 - Device connector rear mounting



1628090

<https://www.phoenixcontact.com/us/products/1628090>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.
product version

M23, Device connector rear mounting, application: Signal, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 16+3, Direction of rotation: Standard, contact connection type: Socket, Solder-in connection, Axial seal, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires
- Application-specific panel mounting optionally with thread or anti-rotation protection and lock nut

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1628090 |
| Packing unit | 12 pc |
| Minimum order quantity | 12 pc |
| Sales key | AB31 |
| Product key | ABRAER |
| GTIN | 4055626381909 |
| Weight per piece (including packing) | 53.158 g |
| Weight per piece (excluding packing) | 46.437 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

CA-19S1NP2HZ00 - Device connector rear mounting



1628090

<https://www.phoenixcontact.com/us/products/1628090>

Technical data

Product properties

| | |
|--------------|-----------------------------------|
| Product type | Circular connectors (device side) |
|--------------|-----------------------------------|

Dimensions

| | |
|--------------------------|---------|
| Length of the solder pin | 3.55 mm |
| | 3.55 mm |

Material specifications

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Connector

Insulating body

| | |
|---|--|
| Coding | N |
| Material (Insulating body) | PA 6.6 |
| Material (Contact) | CuZn |
| Material (Contact surface) | Ni/Au |
| Connection method | Solder-in connection |
| Contact switching type | Socket |
| Application | Signal |
| Number of positions | 19 |
| Direction of rotation | Standard |
| Connection profile | 16+3 |
| Number (Contact group 1) | 3 |
| Contact diameter (Contact group 1) | 1.5 mm |
| Litz wires Min. cross section (Contact group 1) | 0.08 mm ² |
| Litz wires Max. cross section (Contact group 1) | 1 mm ² |
| Rated current Contact (Contact group 1) | 10 A (for max. connection cross section) |
| Rated voltage Contact (Contact group 1) | 48 V AC |
| | 74 V DC |
| Rated surge voltage | 1.5 kV |
| Overvoltage category | III |
| Degree of pollution | 3 |
| Number (Contact group 2) | 16 |
| Contact diameter (Contact group 2) | 1 mm |
| Litz wires Max. cross section (Contact group 2) | 1 mm ² |
| Rated current Contact (Contact group 2) | 8 A |
| Rated voltage Contact (Contact group 2) | 48 V AC |
| | 48 V AC |

Housing

| | |
|------|---------------------|
| Type | Feed-through header |
|------|---------------------|

CA-19S1NP2HZ00 - Device connector rear mounting



1628090

<https://www.phoenixcontact.com/us/products/1628090>

| | |
|-----------------------------------|--------------------------------------|
| Thread type | M23 |
| Design | straight |
| Type of locking | for standard and SPEEDCON interlock |
| Pg screw connection | none |
| Mounting type | Rear wall/screw mounting (M25 x 1,5) |
| Assembly note | Central fastening |
| Material (Housing) | GD-Zn |
| Material (Rotating parts) | CuZn |
| Degree of protection (plugged in) | IP67 |
| Seal for the device | Axial seal |

CA-19S1NP2HZ00 - Device connector rear mounting


1628090

<https://www.phoenixcontact.com/us/products/1628090>



Drawings

Dimensional drawing



Dimensional drawing

CA-19S1NP2HZ00 - Device connector rear mounting

1628090

<https://www.phoenixcontact.com/us/products/1628090>

Schematic diagram




Connector pin assignment


1628090

<https://www.phoenixcontact.com/us/products/1628090>

Drilling plan/solder pad geometry



Drilling plan/solder pad geometry



CA-19S1NP2HZ00 - Device connector rear mounting



1628090

<https://www.phoenixcontact.com/us/products/1628090>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440109 |
| ECLASS-15.0 | 27440109 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003569 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CA-19S1NP2HZ00 - Device connector rear mounting



1628090

<https://www.phoenixcontact.com/us/products/1628090>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | a3cf5a70-3a63-441d-bc85-91f7fca9c0f4 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com