

CA-19S1NP2HZ00 - Device connector rear mounting



1628090

<https://www.phoenixcontact.com/us/products/1628090>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.
product version

M23, Device connector rear mounting, application: Signal, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 16+3, Direction of rotation: Standard, contact connection type: Socket, Solder-in connection, Axial seal, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires
- Application-specific panel mounting optionally with thread or anti-rotation protection and lock nut

Commercial data

Item number	1628090
Packing unit	12 pc
Minimum order quantity	12 pc
Sales key	AB31
Product key	ABRAER
GTIN	4055626381909
Weight per piece (including packing)	53.158 g
Weight per piece (excluding packing)	46.437 g
Customs tariff number	85366990
Country of origin	DE

CA-19S1NP2HZ00 - Device connector rear mounting



1628090

<https://www.phoenixcontact.com/us/products/1628090>

Technical data

Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

Dimensions

Length of the solder pin	3.55 mm
	3.55 mm

Material specifications

Flammability rating according to UL 94	V0
--	----

Connector

Insulating body

Coding	N
Material (Insulating body)	PA 6.6
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Connection method	Solder-in connection
Contact switching type	Socket
Application	Signal
Number of positions	19
Direction of rotation	Standard
Connection profile	16+3
Number (Contact group 1)	3
Contact diameter (Contact group 1)	1.5 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm ²
Litz wires Max. cross section (Contact group 1)	1 mm ²
Rated current Contact (Contact group 1)	10 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	16
Contact diameter (Contact group 2)	1 mm
Litz wires Max. cross section (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A
Rated voltage Contact (Contact group 2)	48 V AC
	48 V AC

Housing

Type	Feed-through header
------	---------------------

CA-19S1NP2HZ00 - Device connector rear mounting



1628090

<https://www.phoenixcontact.com/us/products/1628090>

Thread type	M23
Design	straight
Type of locking	for standard and SPEEDCON interlock
Pg screw connection	none
Mounting type	Rear wall/screw mounting (M25 x 1,5)
Assembly note	Central fastening
Material (Housing)	GD-Zn
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP67
Seal for the device	Axial seal


CA-19S1NP2HZ00 - Device connector rear mounting

1628090

<https://www.phoenixcontact.com/us/products/1628090>



Drawings



Dimensional drawing

CA-19S1NP2HZ00 - Device connector rear mounting

1628090


<https://www.phoenixcontact.com/us/products/1628090>

Schematic diagram




Connector pin assignment

Drilling plan/solder pad geometry



Drilling plan/solder pad geometry



CA-19S1NP2HZ00 - Device connector rear mounting



1628090

<https://www.phoenixcontact.com/us/products/1628090>

Classifications

ECLASS

ECLASS-13.0	27440109
ECLASS-15.0	27440109

ETIM

ETIM 10.0	EC003569
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CA-19S1NP2HZ00 - Device connector rear mounting



1628090

<https://www.phoenixcontact.com/us/products/1628090>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a3cf5a70-3a63-441d-bc85-91f7fca9c0f4

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com