

WP 6070-WVPR - Web panel

1650118

<https://www.phoenixcontact.com/us/products/1650118>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



6th generation rugged web panel, 7.0", format (16:9) VGA, PCAP robust specification

Your advantages

- Robust hardware for harsh environments with 3 mm thick glass, larger heatsink, and stronger housing
- Open and usable in any third-party system
- Ideal for any HTML5 or browser-based visualization
- Can be operated with gloves and suitable for use in damp environments
- Resistant to UV and IR radiation
- Display can be read in sunlight

Commercial data

Item number	1650118
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR17
Product key	DRCADF
GTIN	4067923183711
Weight per piece (including packing)	2,880 g
Weight per piece (excluding packing)	2,038 g
Customs tariff number	84714100
Country of origin	TW

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Operator panel
--------------	----------------

Computer data

Processor	Arm® Cortex®-A53, 1.6 GHz
Operating system	Yocto/Linux®
Data storage system	Flash eMMC, 8 GB
Slots	1x microSD

Display

Display type	17.8 cm / 7"-TFT
Readability in sunlight	yes
Screen resolution	800 x 480 Pixel(s) (WVGA)
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	1000 cd/m² typical (adjustable)
MTBF	50000 h
Color spectrum	16.7 million colors
Reading angle left	89.00 °
Reading angle right	89.00 °
Reading angle top	89.00 °
Reading angle bottom	89.00 °

Interfaces

Interfaces	2x USB 2.0
	1x USB 3.0, Typ C
	1x COM (RS-232/422/485)
Optional interfaces	Without optional interface
Network	1 x Ethernet (10/100/1000 Mbps), RJ45
Bus system	without bus system

System properties

User software	QT browser
---------------	------------

System requirements

Runtime system	Qt Browser
----------------	------------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

WP 6070-WVPR - Web panel



1650118

<https://www.phoenixcontact.com/us/products/1650118>

Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

Material specifications

Color (Housing)	white aluminium (RAL 9006)
Material front plate	Aluminum (natural anodized)
Housing material	Aluminum cast alloy, powder-coated

Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66 (front), IP20 (back)
Ambient temperature (operation)	-30 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Vibration (operation)	5g

1650118

<https://www.phoenixcontact.com/us/products/1650118>

Classifications

ECLASS

ECLASS-13.0	27330201
ECLASS-15.0	27330201

ETIM

ETIM 10.0	EC001412
-----------	----------

1650118

<https://www.phoenixcontact.com/us/products/1650118>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com