

# M17-8ES1N8A9003S - Coupler connector



1628934

<https://www.phoenixcontact.com/us/products/1628934>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M17, Coupler connector, application: Power, series: M17 PRO, straight, shielded: yes, for standard and ONECLICK fast locking system, No. of pos.: 5+3+PE, contact connection type: Socket, Crimp connection, cable diameter range: 5.5 mm ... 9.5 mm, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

The figure shows the product with assembled crimp contacts. Please order crimp contacts separately.

## Your advantages

- Solutions with cross-manufacturer compatibility for standard and fast locking systems
- Modern, consistent design for highly convenient operation
- Easy, cost-effective cable assembly: uniform shielding of M17 to M40

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1628934       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB30          |
| Product key                          | ABRBAG        |
| GTIN                                 | 4055626706399 |
| Weight per piece (including packing) | 68.4 g        |
| Weight per piece (excluding packing) | 51.591 g      |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

## Technical data

### Notes

|                    |  |
|--------------------|--|
| Order information: | Order crimp contacts 5 x 0.6 mm, 4 x Ø 1 mm separately |
|--------------------|--|

### Safety note

|  |  |
|--|--|
| Safety note  | <p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p>  |
|  | <ul style="list-style-type: none"> <li>• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.</li> </ul>  |
|  | <ul style="list-style-type: none"> <li>• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.</li> </ul> |
|  | <ul style="list-style-type: none"> <li>• The products are suitable for applications in plant, controller, and electrical device engineering.</li> </ul>  |
|  | <ul style="list-style-type: none"> <li>• When operating the connectors in outdoor applications, they must be separately protected against environmental influences.</li> </ul>   |
|  | <ul style="list-style-type: none"> <li>• Assembled products may not be manipulated or improperly opened.</li> </ul>  |
|  | <ul style="list-style-type: none"> <li>• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a>).</li> </ul>   |
|  | <ul style="list-style-type: none"> <li>• When using the product in direct connection with third-party manufacturers, the user is responsible.</li> </ul>   |
|  | <ul style="list-style-type: none"> <li>• For operating voltages &gt; 50 V AC, conductive connector housings must be grounded</li> </ul>  |
|  | <ul style="list-style-type: none"> <li>• Ensure that the protective or functional ground has been properly connected.</li> </ul>   |
|  | <ul style="list-style-type: none"> <li>• VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector</li> </ul>  |
|  | <ul style="list-style-type: none"> <li>• Only use tools recommended by Phoenix Contact</li> </ul>  |
|  | <ul style="list-style-type: none"> <li>• The installation notes/Design In documents online on the download page at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a> must be observed for this product.</li> </ul>   |
|  | <ul style="list-style-type: none"> <li>• Operate the connector only when it is fully plugged in and interlocked.</li> </ul>  |
| <ul style="list-style-type: none"> <li>• Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.</li> </ul>  |  |
| <ul style="list-style-type: none"> <li>• Observe the minimum bending radius of the cable. Lay the cable without twisting it.</li> </ul>  |  |
| <ul style="list-style-type: none"> <li>• The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting</li> </ul> |  |

# M17-8ES1N8A9003S - Coupler connector



1628934

<https://www.phoenixcontact.com/us/products/1628934>

warnings (e.g. DIN EN ISO 13732-1:2008-12).

## Product properties

|                |                                 |
|----------------|---------------------------------|
| Product type   | Circular connector (cable-side) |
| Product family | M17 PRO                         |

## Connector

### Insulating body

|   |   |
|---|---|
| Flammability rating according to UL 94          | V0  |
| Insertion/withdrawal cycles                     | 100                                       |
| Connection method                               | Crimp connection                          |
| Contact switching type                          | Socket                                    |
| Application                                     | Power                                     |
| Number of positions                             | 9   |
| Connection profile                              | 5+3+PE                                    |
| Installation height                             | 2000 m                                    |
| Number (Contact group 1)                        | 4   |
| Contact diameter (Contact group 1)              | 1 mm                                      |
| Litz wires Min. cross section (Contact group 1) | 0.06 mm <sup>2</sup>                      |
| Litz wires Max. cross section (Contact group 1) | 1 mm <sup>2</sup>                         |
| Rated current Contact (Contact group 1)         | 14 A (for max. connection cross section)  |
| Rated voltage Contact (Contact group 1)         | 630 V                                     |
| Rated surge voltage                             | 6 kV                                      |
| Overvoltage category                            | III                                       |
| Degree of pollution                             | 3   |
| Number (Contact group 2)                        | 5   |
| Contact diameter (Contact group 2)              | 0.6 mm                                    |
| Litz wires Max. cross section (Contact group 2) | 0.5 mm <sup>2</sup>                       |
| Rated current Contact (Contact group 2)         | 3.6 A (for max. connection cross section) |
| Rated voltage Contact (Contact group 2)         | 60 V                                      |
| Rated surge voltage                             | 1.5 kV                                    |
| Overvoltage category                            | III                                       |
| Degree of pollution                             | 3   |

### Housing

|                                   |   |
|-----------------------------------|---|
| Type                              | Coupling housing                              |
| Thread type                       | M17   |
| Design                            | straight                                      |
| Type of locking                   | for standard and ONECLICK fast locking system |
| Pg screw connection               | none  |
| Material (Housing)                | GD-Zn   |
| Degree of protection (plugged in) | IP67<br>IP68 (2 m / 24 h)                     |

### Seal

# M17-8ES1N8A9003S - Coupler connector



1628934

<https://www.phoenixcontact.com/us/products/1628934>

|                         |                   |
|-------------------------|-------------------|
| External cable diameter | 5.5 mm ... 9.5 mm |
|-------------------------|-------------------|

## Environmental and real-life conditions

### Ambient conditions

|  |  |
|--|--|
| Ambient temperature (operation)          | -40 °C ... 105 °C (see derating curve) |
| Permissible humidity (storage/transport) | 50 % ... 65 %                          |

# M17-8ES1N8A9003S - Coupler connector

1628934

<https://www.phoenixcontact.com/us/products/1628934>

## Drawings

Schematic diagram



Connector pin assignment

Diagram



$I$  = current strength,  $\vartheta$  = ambient temperature, 3x 14 A + 2x 2 A constant

# M17-8ES1N8A9003S - Coupler connector

1628934

<https://www.phoenixcontact.com/us/products/1628934>



$I$  = current strength,  $\vartheta$  = ambient temperature, 3x 14 A + 2x 2 A constant

# M17-8ES1N8A9003S - Coupler connector




1628934

<https://www.phoenixcontact.com/us/products/1628934>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1628934>

|  <b>UL Listed</b><br>Approval ID: E468743 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
| Power  | 600 V                 | 10 A                  | - 18              | 1                           |
| Signal   | 60 V                  | 2 A                   | - 20              | 1                           |

|  <b>cUL Listed</b><br>Approval ID: E468743 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
| Power   | 600 V                 | 8 A                   | - 18              | -                           |
| Signal  | 60 V                  | 2 A                   | - 20              | -                           |

# M17-8ES1N8A9003S - Coupler connector



1628934

<https://www.phoenixcontact.com/us/products/1628934>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# M17-8ES1N8A9003S - Coupler connector



1628934

<https://www.phoenixcontact.com/us/products/1628934>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)