

# VS-BU-KX-50-RG58 - D-SUB coaxial contact



1655577

<https://www.phoenixcontact.com/us/products/1655577>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coaxial contact, for D-SUB combination inserts, solder cup, pin, straight, for cable RG 58, gold-plated

## Commercial data

Item number	1655577
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAC
GTIN	4046356029483
Weight per piece (including packing)	2.62 g
Weight per piece (excluding packing)	2.308 g
Customs tariff number	85366910
Country of origin	CZ

# VS-BU-KX-50-RG58 - D-SUB coaxial contact



1655577

<https://www.phoenixcontact.com/us/products/1655577>

## Technical data

### Product properties

Product type	Contacts
Series	HC-M-04-KOAX
Contact material type	turned

### Electrical properties


Rated current (Maximum load current)	2 A
Resistance (Insulation resistance)	$\geq 500 \text{ M}\Omega$

### Connection data

#### Connection technology

Contact connection type	Coaxial
Connection method	Solder cup

### Dimensions

Dimensional drawing	
Width [w]	5.95 mm
Height [h]	5.95 mm
Length [l]	24.6 mm
External cable diameter	5.2 mm

### Material specifications

Material Contact	Metal
------------------	-------

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	$\geq 500$
Insertion force	$\leq 7 \text{ N}$
Withdrawal force	$\leq 7 \text{ N}$

### Characteristics

#### Measuring system

Resistance: Insulation resistance	$\geq 500 \text{ M}\Omega$
-----------------------------------	----------------------------

### Environmental and real-life conditions

#### Ambient conditions

# VS-BU-KX-50-RG58 - D-SUB coaxial contact



1655577

<https://www.phoenixcontact.com/us/products/1655577>

Ambient temperature (operation)	-55 °C ... 135 °C
---------------------------------	-------------------

## Mounting

Mounting type	Solder connection
---------------	-------------------

# VS-BU-KX-50-RG58 - D-SUB coaxial contact




1655577

<https://www.phoenixcontact.com/us/products/1655577>

## Drawings

Dimensional drawing



Cable connection

# VS-BU-KX-50-RG58 - D-SUB coaxial contact



1655577

<https://www.phoenixcontact.com/us/products/1655577>

## Classifications

### ECLASS

ECLASS-13.0	27440392
ECLASS-15.0	27440392

### ETIM

ETIM 10.0	EC002943
-----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

# VS-BU-KX-50-RG58 - D-SUB coaxial contact



1655577

<https://www.phoenixcontact.com/us/products/1655577>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b6f0445f-e008-4692-a7fe-559f9d64b8cb

### EF3.1 Climate Change

CO2e kg	0.751 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)