

# VS-PPC-C1-RJ45-POBK-PG9-8Q5 - RJ45 connector



1657834

<https://www.phoenixcontact.com/us/products/1657834>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, degree of protection: IP65/IP67, number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), material: Plastic, connection method: IDC fast connection, connection cross section: AWG 26- 22, cable outlet: straight, color: black, Ethernet

## Commercial data

Item number	1657834
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNOAA
GTIN	4046356131902
Weight per piece (including packing)	32.1 g
Weight per piece (excluding packing)	29 g
Customs tariff number	85366990
Country of origin	DE

# VS-PPC-C1-RJ45-POBK-PG9-8Q5 - RJ45 connector



1657834

<https://www.phoenixcontact.com/us/products/1657834>

## Technical data

### Product properties

Product type	Data connector (cable side)
Type	RJ45
Sensor type	Ethernet
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Shielded	yes
Cable outlet	straight

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Nominal voltage $U_N$	48 V
Contact resistance	0.001 $\Omega$ (Wire – IDC) 0.005 $\Omega$ (Litz wires – IDC)
Transmission medium	Copper
Transmission speed	1 Gbps
Transmission characteristics (category)	CAT5
Transmission speed	1 Gbps

### Connection data

#### Connection technology

Connection method	IDC fast connection
Connection cross section AWG	26 ... 22 (solid) 26 ... 22 (flexible)
Conductor cross-section	0.13 mm <sup>2</sup> ... 0.32 mm <sup>2</sup> (solid) 0.14 mm <sup>2</sup> ... 0.36 mm <sup>2</sup> (flexible)

### Dimensions

Width	22 mm
Height	30 mm
Length	70 mm

### Material specifications

Color	black
Material	Plastic
Flammability rating according to UL 94	V0

# VS-PPC-C1-RJ45-POBK-PG9-8Q5 - RJ45 connector



1657834

<https://www.phoenixcontact.com/us/products/1657834>

Seal material, O-ring	NBR
Seal material cable seal	TPE
Seal material	NBR
Seal material, pin connector pattern	NBR
Housing material	Plastic
Cable seal material	TPE
Contact material	CuSn
Contact surface material	Au/Ni
Contact carrier material	PC
O-ring material	NBR
Material for screw connection	PA

## Cable/line

External cable diameter	5 mm ... 8 mm
Cable cross section	0.14 mm <sup>2</sup>

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

## Standards and regulations

Standards/specifications	IEC PAS 61076-3-117
--------------------------	---------------------

# VS-PPC-C1-RJ45-POBK-PG9-8Q5 - RJ45 connector





1657834

<https://www.phoenixcontact.com/us/products/1657834>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1657834>

 <b>cUL Recognized</b> Approval ID: E118976				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	50 V	1.75 A	- 22	-

 <b>UL Recognized</b> Approval ID: E118976				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	50 V	1.75 A	- 22	-

# VS-PPC-C1-RJ45-POBK-PG9-8Q5 - RJ45 connector



1657834

<https://www.phoenixcontact.com/us/products/1657834>

## Classifications

### ECLASS

ECLASS-15.0	27440114
ECLASS-13.0	27440290

### ETIM

ETIM 10.0	EC002636
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-PPC-C1-RJ45-POBK-PG9-8Q5 - RJ45 connector



1657834

<https://www.phoenixcontact.com/us/products/1657834>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1) 2-(2H-benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol (UV-329)(CAS: 3147-75-9)
SCIP	1baed9af-d769-4942-8510-17e3e55eae92

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)