

VS-PP-F-SCRJ - DIN rail adapter



1658121

<https://www.phoenixcontact.com/us/products/1658121>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch panel, SC-RJ, DIN rail mounting, IP20, 1 slot, socket/socket, can be used for glass, multi-mode, PCF, and polymer fibers

Product description

Freenet system

Your advantages

- Compact design
- DIN rail mounting
- Individual marking field
- Can be used for all fiber types

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1658121 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB15 |
| Product key | ABNLAA |
| GTIN | 4046356149167 |
| Weight per piece (including packing) | 48.3 g |
| Weight per piece (excluding packing) | 48.3 g |
| Customs tariff number | 85367000 |
| Country of origin | CH |

VS-PP-F-SCRJ - DIN rail adapter



1658121

<https://www.phoenixcontact.com/us/products/1658121>

Technical data

Product properties

| | |
|---------------------|--|
| Product type | Network distributor box |
| Housing type | DIN rail adapter |
| Type | SCRJ |
| Number of positions | 2 |
| Connection profile | SCRJ in accordance with DIN EN 50377-6-1 |
| Number of slots | 1 |

Electrical properties

| | |
|---------------------|----|
| Transmission medium | FO |
|---------------------|----|

Connection data

Connection technology

| | |
|-------------------|----------|
| Connection method | Coupling |
|-------------------|----------|

Dimensions

| | |
|--------|---------|
| Width | 26.8 mm |
| Height | 71 mm |
| Length | 81.4 mm |

Mechanical characteristics

| | |
|------------------|---------|
| Ferrule diameter | 2.50 mm |
|------------------|---------|

Material specifications

| | |
|--|-------------------|
| Color | gray |
| Flammability rating according to UL 94 | V0 |
| Ferrule material | Zirconia ceramics |
| Housing material | PC-GF |
| Material, protective cover | PC |

Cable/line

| | |
|-------------------------|-----------------|
| External cable diameter | 4.5 mm ... 9 mm |
|-------------------------|-----------------|

FO cable

| | |
|------------|---------------|
| Fiber type | GOF, PCF, POF |
|------------|---------------|

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 500 |
|-----------------------------|-------|

Environmental and real-life conditions

Ambient conditions

VS-PP-F-SCRJ - DIN rail adapter



1658121

<https://www.phoenixcontact.com/us/products/1658121>

| | |
|---|------------------|
| Degree of protection | IP20 |
| | IP20 |
| Ambient temperature (operation) | -10 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

VS-PP-F-SCRJ - DIN rail adapter



1658121

<https://www.phoenixcontact.com/us/products/1658121>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19170113 |
| ECLASS-15.0 | 19170113 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002699 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43223300 |
|-------------|----------|

VS-PP-F-SCRJ - DIN rail adapter



1658121

<https://www.phoenixcontact.com/us/products/1658121>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com