

# VS-08-RJ45-5-Q/IP67-BK - RJ45 connector



1658493

<https://www.phoenixcontact.com/us/products/1658493>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, design: RJ45, degree of protection: IP67, number of positions: 8, 1 Gbps, CAT5, material: Plastic, connection method: IDC fast connection, connection cross section: AWG 26- 23, cable outlet: straight, color: jet black RAL 9005, Ethernet

## Your advantages

- Assembly without special tools
- IP65/67
- High-quality and inexpensive solution in the IP protection zone
- Simple operation

## Commercial data

Item number	1658493
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNNAA
GTIN	4046356163163
Weight per piece (including packing)	32.1 g
Weight per piece (excluding packing)	27.02 g
Customs tariff number	85366990
Country of origin	DE

# VS-08-RJ45-5-Q/IP67-BK - RJ45 connector



1658493

<https://www.phoenixcontact.com/us/products/1658493>

## Technical data

### Product properties

Product type	Data connector (cable side)
Type	RJ45
Sensor type	Ethernet
Number of positions	8
Connection profile	RJ45
No. of cable outlets	1
Shielded	yes
Cable outlet	straight

### Insulation characteristics

Overvoltage category	I
Degree of pollution	2

### Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated current	1.75 A
Nominal voltage $U_N$	48 V
Contact resistance	0.001 $\Omega$ (Wire – IDC) 0.005 $\Omega$ (Litz wires – IDC)
Transmission medium	Copper
Transmission speed	1 Gbps
Transmission characteristics (category)	CAT5
Transmission speed	1 Gbps
Power transmission	PoE++ in accordance with: IEEE 802.3bt

### Connection data

#### Connection technology

Connection method	IDC fast connection
Connection cross section AWG	26 ... 23 (solid) 26 ... 23 (flexible)
Conductor cross-section	0.14 mm <sup>2</sup> ... 0.36 mm <sup>2</sup> (solid) 0.14 mm <sup>2</sup> ... 0.36 mm <sup>2</sup> (flexible)

### Dimensions

Width	38.4 mm
Height	22.4 mm
Length	80 mm

### Material specifications

Color	jet black RAL 9005
Material	Plastic

# VS-08-RJ45-5-Q/IP67-BK - RJ45 connector



1658493

<https://www.phoenixcontact.com/us/products/1658493>

Flammability rating according to UL 94	V0
Housing material	Plastic
Cable seal material	NBR
Contact material	Copper alloy
Contact surface material	Gold over nickel
Contact carrier material	PC
O-ring material	FPM

## Cable/line

External cable diameter	5 mm ... 8.5 mm
Cable cross section	0.14 mm <sup>2</sup>

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 1000
-----------------------------	--------

# VS-08-RJ45-5-Q/IP67-BK - RJ45 connector





1658493

<https://www.phoenixcontact.com/us/products/1658493>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1658493>

 <b>cUL Recognized</b> Approval ID: E118976				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	50 V	1.75 A	- 22	-

 <b>UL Recognized</b> Approval ID: E118976				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	50 V	1.75 A	- 22	-

# VS-08-RJ45-5-Q/IP67-BK - RJ45 connector



1658493

<https://www.phoenixcontact.com/us/products/1658493>

## Classifications

### ECLASS

ECLASS-13.0	27440390
ECLASS-15.0	27440114

### ETIM

ETIM 10.0	EC002636
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-08-RJ45-5-Q/IP67-BK - RJ45 connector



1658493

<https://www.phoenixcontact.com/us/products/1658493>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1) 2-(2H-benzotriazol-2-yl)-4-(1,1,3,3-tetramethylbutyl)phenol (UV-329)(CAS: 3147-75-9)
SCIP	e081779b-caa1-4134-9633-50ed82d8281e

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)