

VS-CAT6-4X2X26 AWG/7/100 - Installation cable



1658891

<https://www.phoenixcontact.com/us/products/1658891>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CAT6-S/FTP cable, 4 x 2 x 26 AWG, stranded, (7-wire) shielded, outer sheath: Halogen-free PUR, outside diameter 6.7 mm, RAL 5021 (water blue), cable ring 100 m

Commercial data

Item number	1658891
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LFA
GTIN	4046356166140
Weight per piece (including packing)	4,451.4 g
Weight per piece (excluding packing)	4,451.4 g
Customs tariff number	85444290
Country of origin	DE

VS-CAT6-4X2X26 AWG/7/100 - Installation cable



1658891

<https://www.phoenixcontact.com/us/products/1658891>

Technical data

Product properties

Product type	Data cable by the meter
Number of positions	8
Shielded	yes


Electrical properties

Transmission characteristics (category)	CAT6
---	------

Cable/line

Cable length	100 m
--------------	-------

Ethernet [94F]

Dimensional drawing	
Cable weight	43 kg/km
Number of positions	8
Shielded	yes
Cable type	Ethernet [94F]
Conductor structure	4x2xAWG26/7; S/FTP
Signal runtime	5.3 ns/m
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross-section	4x 2x 0.14 mm ²
Wire diameter incl. insulation	1.04 mm
External cable diameter	6.40 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021
Conductor material	Bare Cu litz wires
Material wire insulation	PE
Single wire, color	white/blue-blue, white/orange-orange, white/green-green, white/brown-brown
Thickness, insulation	0.28 mm (Signal line) 0.65 mm (Outer cable sheath)
Twisted pairs	2 cores to the pair
Type of pair shielding	Aluminum-lined polyester foil
Overall twist	4 pairs

VS-CAT6-4X2X26 AWG/7/100 - Installation cable



1658891

<https://www.phoenixcontact.com/us/products/1658891>

Optical shield covering	70 %
Max. conductor resistance	≤ 290 Ω/km (at 20 °C)
Insulation resistance	≥ 500 MΩ*km (at 20 °C)
Wave impedance	100 Ω ±5 Ω (at 100 MHz)
Nominal voltage, cable	≤ 100 V (at 20 °C)
Test voltage Core/Core	700 V (50 Hz, 1 min.)
Test voltage Core/Shield	700.00 V (50 Hz, 1 min.)
Smallest bending radius, fixed installation	25.6 mm
Smallest bending radius, movable installation	51.2 mm
Tensile strength	≤ 100 N
Shield attenuation	≥ 80.00 dB (at 30 ... 100 MHz)
Halogen-free	according to IEC 60754-1
Flame resistance	IEC 60332-1-2
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-40 °C ... 70 °C (cable, fixed installation) -10 °C ... 50 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation) (Cable, fixed installation)	-20 °C ... 60 °C (cable, fixed installation)
Ambient temperature (operation) (Cable, flexible installation)	0 °C ... 50 °C (Cable, flexible installation)

VS-CAT6-4X2X26 AWG/7/100 - Installation cable



1658891

<https://www.phoenixcontact.com/us/products/1658891>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

VS-CAT6-4X2X26 AWG/7/100 - Installation cable



1658891

<https://www.phoenixcontact.com/us/products/1658891>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com