

VS-CAT7-4X2X26 AWG/7-BK/100 - Installation cable



1658914

<https://www.phoenixcontact.com/us/products/1658914>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CAT7-S/FTP cable, 4 x 2 x 26 AWG, stranded, (7-wire) shielded, outer sheath: Halogen-free PUR, outside diameter 7.9 mm, RAL 9005 (black), cable ring 100 m

Commercial data

Item number	1658914
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	AF1LFA
GTIN	4046356166126
Weight per piece (including packing)	6,222 g
Weight per piece (excluding packing)	6,222 g
Customs tariff number	85444290
Country of origin	DE

VS-CAT7-4X2X26 AWG/7-BK/100 - Installation cable



1658914

<https://www.phoenixcontact.com/us/products/1658914>

Technical data

Product properties

Product type	Data cable by the meter
Number of positions	8
Shielded	yes

Electrical properties

Transmission characteristics (category)	CAT7
---	------

Cable/line

Cable length	100 m
Cable weight	44 kg/km
Number of positions	8
Shielded	yes
Conductor structure	4x2xAWG26/7; S/FTP
Conductor type	Round cable
Signal runtime	0.46 ns/m
Signal speed	0.72 c
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross-section	4x 2x 0.14 mm ²
Wire diameter incl. insulation	1 mm
External cable diameter	7.80 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	Cell PE
Single wire, color	white-blue, white-orange, white-green, white-brown
Twisted pairs	2 cores to the pair
Type of pair shielding	Aluminum-lined polyester foil
Overall twist	4 pairs for core
Optical shield covering	65 %
Max. conductor resistance	≤ 150 Ω/km
Insulation resistance	≥ 5 GΩ*km
Coupling resistance	5.00 mΩ/m (at 10 MHz)
Wave impedance	100 Ω ±5 % (at 100 MHz)
Working capacitance	42 pF
Nominal voltage, cable	125 V
Test voltage	1000 V
Smallest bending radius, fixed installation	40 mm
Shield attenuation	60.00 dB (up to 1000 MHz)
Resistance to oil	in accordance with DIN EN 60811-2-1

VS-CAT7-4X2X26 AWG/7-BK/100 - Installation cable



1658914

<https://www.phoenixcontact.com/us/products/1658914>

Ambient temperature (operation)	-40 °C ... 70 °C (cable, fixed installation)
	-10 °C ... 50 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation) (Cable, fixed installation)	-40 °C ... 70 °C (cable, fixed installation)
Ambient temperature (operation) (Cable, flexible installation)	0 °C ... 50 °C (Cable, flexible installation)

VS-CAT7-4X2X26 AWG/7-BK/100 - Installation cable



1658914

<https://www.phoenixcontact.com/us/products/1658914>

Classifications

ECLASS

ECLASS-13.0	27061801
ECLASS-15.0	27061801

VS-CAT7-4X2X26 AWG/7-BK/100 - Installation cable



1658914

<https://www.phoenixcontact.com/us/products/1658914>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com