

# SACB-4Q/4P-L-SC - Distributor box



1662939

<https://www.phoenixcontact.com/us/products/1662939>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box, application: Standard, connection method: QUICKON, 0.34 mm<sup>2</sup> ... 0.75 mm<sup>2</sup>, number of slots: 4, number of positions: 4, slot assignment: single, status display: yes, PNP; master cable connection: Spring-cage connection 180°, shielding: no

## Your advantages

- Safety in the field, thanks to molded housing and high degree of protection
- Convenient: increased machine availability thanks to quick and easy diagnostics
- Innovative and time-saving assembly with insulation displacement connection
- Flexible: distributor box with connector hood for on-site assembly

## Commercial data

Item number	1662939
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF41
Product key	AF3DBC
GTIN	4017918137489
Weight per piece (including packing)	199.1 g
Weight per piece (excluding packing)	166.1 g
Customs tariff number	85366990
Country of origin	PL

# SACB-4Q/4P-L-SC - Distributor box



1662939

<https://www.phoenixcontact.com/us/products/1662939>

## Technical data

### Notes

Assembly note	<b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.
Note on application	Unused slots are to be sealed off prior to commissioning. Suitable sealing elements are to be found under "Accessories".

### Product properties

Product type	Distributor box
Application	Standard
Number of positions	4
Number of slots	4
LED	yes

### System properties

#### Local diagnostics

Monitored function	Supply voltage per module
Optical representation	Green LED

### Electrical properties

Max. operating voltage $U_{max}$	30 V DC
Local diagnostics	Supply voltage per module Green LED
	Status display I/O Yellow LED
Nominal voltage $U_N$	24 V DC
Rated current, total	12 A
Max. current carrying capacity per path	4 A
Current carrying capacity per slot	4 A

### Connection data

#### Conductor connection

Sensor/actuator connection system	QUICKON
Conductor cross-section Flexible signal line	0.14 mm <sup>2</sup> ... 1 mm <sup>2</sup>
Conductor cross-section Flexible power supply	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Connection cross section AWG Flexible signal line	26 ... 17
Connection cross section AWG Flexible power supply	24 ... 16
Stripping length Signal line	10 mm
Stripping length of the sheath	70 mm (Master cable)
Tightening torque, union nut	2.5 Nm

#### Connection assignment

1 / 4 (A) = 1 / 4

# SACB-4Q/4P-L-SC - Distributor box



1662939

<https://www.phoenixcontact.com/us/products/1662939>

Slot/position = Wire color or connection	2 / 4 (A) = 2 / 4
	3 / 4 (A) = 3 / 4
	4 / 4 (A) = 4 / 4
	1-4 / 1 (+ 24 V) = U <sub>N</sub>
	1-4 / 3 (0 V) = 0 V
	1-4 / 5 (PE) = PE

## Signaling

Status display present	yes
------------------------	-----

## Dimensions

Dimensional drawing	
Width	60 mm
Height	44 mm
Length	132 mm
Wrench size, union nut	22 mm

## Material specifications

Material Housing	PA
Material Molding compound	PUR
Flammability rating according to UL 94	V0
Contact material	Steel/copper
Contact surface material	Sn
Contact carrier material	PA 6.6
Material of contact, master cable side	CuZn
Material of the contact carrier on the master cable side	PA 6.6 V0
Material of contact surface, master cable side	NiSn
Wire insulation material	PVC / PE

## Cable/line

External cable diameter	6.5 mm ... 9.5 mm
Connection method	Spring-cage connection

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67

# SACB-4Q/4P-L-SC - Distributor box



1662939

<https://www.phoenixcontact.com/us/products/1662939>

Ambient temperature (operation)	-25 °C ... 60 °C
	-25 °C ... 50 °C (when the conductor is connected. Specifications of the cable manufacturer must also be observed.)

# SACB-4Q/4P-L-SC - Distributor box




1662939

<https://www.phoenixcontact.com/us/products/1662939>

## Drawings

Dimensional drawing




# SACB-4Q/4P-L-SC - Distributor box



1662939


<https://www.phoenixcontact.com/us/products/1662939>

Schematic diagram



QUICKON connection, 4-pos.

Circuit diagram



# SACB-4Q/4P-L-SC - Distributor box



1662939

<https://www.phoenixcontact.com/us/products/1662939>

## Classifications

### ECLASS

ECLASS-13.0	27440111
ECLASS-15.0	27440111

### UNSPSC

UNSPSC 21.0	31251501
-------------	----------

# SACB-4Q/4P-L-SC - Distributor box



1662939

<https://www.phoenixcontact.com/us/products/1662939>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)