

# CUC-IB6G-J1ST-AT/R4T - Filtered RJ45 PCB connectors



1664022

<https://www.phoenixcontact.com/us/products/1664022>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Filtered RJ45 PCB connectors, 1x1 single-port, connection direction of the connector to the PCB: 90 °, Tab up, Shielded, number of positions: 8, 1 Gbps, THT, THD, Wave, IP20, type of packaging: Tray

## Your advantages

- Simplified Ethernet design process thanks to integrated filtering
- Reduced PCB complexity and reduced EMC risks
- High mechanical stability when connecting the female connector to the PCB using through-hole technology (THT)
- Tray packing
- Space-saving due to the compact design
- Outstanding EMI performance
- Enables space-saving PCB design while simultaneously reducing the BOM thanks to integrated filters and transformers
- Ideal for demanding industrial applications due to the high shock and vibration resistance as well as the extended temperature range

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1664022       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | AB12          |
| Product key                          | ABNAFA        |
| GTIN                                 | 4067923204287 |
| Weight per piece (including packing) | 8.89 g        |
| Weight per piece (excluding packing) | 6.3 g         |
| Customs tariff number                | 85366930      |
| Country of origin                    | CN            |

# CUC-IB6G-J1ST-AT/R4T - Filtered RJ45 PCB connectors



1664022

<https://www.phoenixcontact.com/us/products/1664022>

## Technical data

### Product properties

|                     |                         |
|---------------------|-------------------------|
| Slots               | 1x1 single-port         |
| Orientation to PCB  | 90.00 °                 |
| Type                | THD                     |
| Number of positions | 8 (8P8C)                |
| Type of locking     | Snap-in locking, Tab up |
| Shielding           | Shielded                |
| Processing notes    | Wave                    |
| Type of packaging   | Tray                    |
| Transmission speed  | 1 Gbps (1000BASE-T)     |

### Electrical properties

|                               |                         |
|-------------------------------|-------------------------|
| Pollution degree              | 2 (IEC 60664-1)         |
| Overvoltage category          | I (IEC 60664-1)         |
| Rated surge voltage           | 1.5 kV DC (IEC 60664-1) |
| Rated current                 | 0.5 A                   |
| Insulation resistance         | > 500 MΩ (IEC 60603-7)  |
| Test voltage (Contact/shield) | 1.5 kV DC (IEC 60603-7) |

### Dimensions

|                  |          |
|------------------|----------|
| Length           | 21.5 mm  |
| Width            | 15.75 mm |
| Height           | 17.4 mm  |
| Installed height | 13.80 mm |
| Data pin length  | 3.20 mm  |

### Material specifications

|                                                       |                                |
|-------------------------------------------------------|--------------------------------|
| Material Contact carrier                              | LCP                            |
| Flame resistance                                      | UL 94 V0                       |
| Halogen-free                                          | yes                            |
| Material Housing                                      | Copper alloy                   |
| Material Housing coating                              | Ni (0.762 µm min / 30 µ" min)  |
| Material Housing pin coating (top layer/selective)    | Sn (3,048 µm min / 120 µ" min) |
| Material Contact                                      | Phosphor bronze                |
| Material Solder contact coating (intermediate layer)  | Ni (1,016 µm min / 40 µ" min)  |
| Material Solder contact coating (top layer/selective) | Sn (3,048 µm min / 120 µ" min) |
| Material Plug contact coating (top layer/selective)   | Au (0.762 µm/30 µ")            |
| Material Plug contact coating (intermediate layer)    | Ni (1,270 µm min / 50 µ" min)  |

### Mechanical properties

#### Mechanical data

# CUC-IB6G-J1ST-AT/R4T - Filtered RJ45 PCB connectors



1664022

<https://www.phoenixcontact.com/us/products/1664022>

|                             |                      |
|-----------------------------|----------------------|
| Insertion/withdrawal cycles | > 750 (IEC 60603-7)  |
| Insertion force             | < 20 N (IEC 60603-7) |
| Withdrawal force            | < 20 N (IEC 60603-7) |

## Environmental and real-life conditions

### Ambient conditions

|                                         |                    |
|-----------------------------------------|--------------------|
| Ambient temperature (operation)         | -40 °C ... 85 °C   |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C   |
| Degree of protection (plugged in)       | IP20 (IEC 60603-7) |

### Test specification for vibration - sine (IEC 60068-2-6)

|              |                               |
|--------------|-------------------------------|
| Acceleration | 100 m/s <sup>2</sup>          |
| Frequency    | 10 ... 500 Hz                 |
| Amplitude    | 0.35 mm                       |
| Cycles       | 10 cycles per axis, 20 sweeps |
| Sweep speed  | 1 octave/min                  |

### Test specification Shock (IEC 60068-2-27)

|              |                      |
|--------------|----------------------|
| Pulse shape  | Half-sine            |
| Acceleration | 300 m/s <sup>2</sup> |


## Mounting

### Processing notes


|               |     |
|---------------|-----|
| Mounting type | THT |
|---------------|-----|

1664022  
<https://www.phoenixcontact.com/us/products/1664022>

Drawings



Classification wave soldering profile



# CUC-IB6G-J1ST-AT/R4T - Filtered RJ45 PCB connectors



1664022

<https://www.phoenixcontact.com/us/products/1664022>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1664022>



**cULus Recognized**

Approval ID: E140403-20250401

# CUC-IB6G-J1ST-AT/R4T - Filtered RJ45 PCB connectors



1664022

<https://www.phoenixcontact.com/us/products/1664022>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002637 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CUC-IB6G-J1ST-AT/R4T - Filtered RJ45 PCB connectors



1664022

<https://www.phoenixcontact.com/us/products/1664022>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)