

CUC-IA1G-J1ST-AB/R4T-PL1 - Filtered RJ45 PCB connectors



1664106

<https://www.phoenixcontact.com/us/products/1664106>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Filtered RJ45 PCB connectors, 1x1 single-port, connection direction of the connector to the PCB: 90 °, Tab down, Shielded, shield springs, LED (green, yellow), number of positions: 8, 1 Gbps, THT, THD, Wave, IP20

Your advantages

- Simplified Ethernet design process thanks to integrated filtering
- Reduced PCB complexity and reduced EMC risks
- High mechanical stability when connecting the female connector to the PCB using through-hole technology (THT)
- Tray packing
- Space-saving due to the compact design
- Outstanding EMI performance
- Enables space-saving PCB design while simultaneously reducing the BOM thanks to integrated filters and transformers
- Ideal for demanding industrial applications due to the high shock and vibration resistance as well as the extended temperature range

Commercial data

Item number	1664106
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AB12
Product key	ABNAFA
GTIN	4067923203471
Weight per piece (including packing)	8.6 g
Weight per piece (excluding packing)	6.3 g
Customs tariff number	85366930
Country of origin	CN

CUC-IA1G-J1ST-AB/R4T-PL1 - Filtered RJ45 PCB connectors



1664106

<https://www.phoenixcontact.com/us/products/1664106>

Technical data

Product properties

Slots	1x1 single-port
Orientation to PCB	90.00 °
Type	THD
Number of positions	8 (8P8C)
Type of locking	Snap-in locking, Tab down
Shielding	Shielded, shield springs
Status display	LED (green, yellow)
Processing notes	Wave
Transmission speed	1 Gbps (1000BASE-T)

Electrical properties

Pollution degree	2 (IEC 60664-1)
Overvoltage category	I (IEC 60664-1)
Rated surge voltage	1.5 kV (IEC 60664-1)
Rated current	0.5 A
Insulation resistance	> 500 MΩ (IEC 60603-7)
Test voltage (Contact/shield)	1.5 kV DC (IEC 60603-7)

Dimensions

Length	21.35 mm
Width	15.9 mm
Height	17.13 mm
Installed height	13.63 mm
Data pin length	3.50 mm

Material specifications

Material Contact carrier	LCP
Flame resistance	UL 94 V0
Halogen-free	yes
Material Housing	Copper alloy
Material Housing coating	Ni (0.762 µm min / 30 µ" min)
Material Housing pin coating (top layer/selective)	Sn (3,048 µm min / 120 µ" min)
Material Contact	Phosphor bronze
Material Solder contact coating (intermediate layer)	Ni (1,016 µm min / 40 µ" min)
Material Solder contact coating (top layer/selective)	Sn (3,048 µm min / 120 µ" min)
Material Plug contact coating (top layer/selective)	Au (0.762 µm/30 µ")
Material Plug contact coating (intermediate layer)	Ni (1,270 µm min / 50 µ" min)

Mechanical properties

Mechanical data

CUC-IA1G-J1ST-AB/R4T-PL1 - Filtered RJ45 PCB connectors



1664106

<https://www.phoenixcontact.com/us/products/1664106>

Insertion/withdrawal cycles	> 750 (IEC 60603-7)
Insertion force	< 20 N (IEC 60603-7)
Withdrawal force	< 20 N (IEC 60603-7)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Degree of protection (plugged in)	IP20 (IEC 60603-7)

Test specification for vibration - sine (IEC 60068-2-6)

Acceleration	100 m/s ²
Frequency	10 ... 500 Hz
Amplitude	0.35 mm
Cycles	10 cycles per axis, 20 sweeps
Sweep speed	1 octave/min

Test specification Shock (IEC 60068-2-27)

Pulse shape	Half-sine
Acceleration	300 m/s ²

Mounting

Processing notes

Mounting type	THT
---------------	-----


CUC-IA1G-J1ST-AB/R4T-PL1 - Filtered RJ45 PCB connectors



1664106
https://www.phoenixcontact.com/us/products/1664106


Drawings

Diagram



Classification wave soldering profile

Circuit diagram



Circuit diagram

CUC-IA1G-J1ST-AB/R4T-PL1 - Filtered RJ45 PCB connectors



1664106

<https://www.phoenixcontact.com/us/products/1664106>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1664106>



cULus Recognized

Approval ID: E140403-20250401

CUC-IA1G-J1ST-AB/R4T-PL1 - Filtered RJ45 PCB connectors



1664106

<https://www.phoenixcontact.com/us/products/1664106>

Classifications

ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

ETIM

ETIM 10.0	EC002637
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-IA1G-J1ST-AB/R4T-PL1 - Filtered RJ45 PCB connectors



1664106

<https://www.phoenixcontact.com/us/products/1664106>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com