# M23-06P1N8A80DUS - Cable connector

1629188

https://www.phoenixcontact.com/us/products/1629188

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the product with assembled crimp contacts. Please order crimp contacts separately.

M23, Cable connector, application: Signal, series: M23 PRO, straight, shielded: yes, ONECLICK fast locking system, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 3 mm ... 15 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- Solutions with cross-manufacturer compatibility for standard and fast locking systems
- ONECLICK fast locking system with an optically, haptically, and acoustically clear locking position
- Reliable under the harshest conditions: cable connectors with vibration brake
- Modern, consistent design for highly convenient operation
- Easy, cost-effective cable assembly: uniform shielding of M17 to M40

## Commercial data

| | |
|---|---|
| Item number | 1629188 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB30 |
| Product key | ABRABB |
| GTIN | 4055626618210 |
| Weight per piece (including packing) | 114.5 g |
| Weight per piece (excluding packing) | 99.09 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

# Technical data

## Notes

| | |
|---|---|
| Order information: | Order crimp contacts 6 x Ø 2 mm separately |

## Product properties

| | |
|---|---|
| Product type | Circular connector (cable-side) |
| Product family | M23 PRO |

## Connector

### Insulating body

| | |
|---|---|
| Note | Order information: Order crimp contacts 6 x Ø 2 mm separately |
| Coding | N |
| Material (Insulating body) | PA 6.6 |
| Insertion/withdrawal cycles | 100 |
| Connection method | Crimp connection |
| Contact switching type | Pin |
| Application | Signal |
| Number of positions | 6 |
| Direction of rotation | Standard |
| Connection profile | 6 |
| Installation height | 2000 m |
| Number (Signal contacts) | 6 |
| Contact diameter (Signal contacts) | 2 mm |
| Litz wires Min. cross section (Signal contacts) | 0.5 mm² |
| Litz wires Max. cross section (Signal contacts) | 2.5 mm² |
| Rated current Contact (Signal contacts) | 20 A (for max. connection cross section) |
| Rated voltage Contact (Signal contacts) | 300 V |
| Rated surge voltage | 2.5 kV |
| Overvoltage category | II |
| Degree of pollution | 3 |

### Housing

| | |
|---|---|
| Type | Cable connector housing |
| Thread type | M23 |
| Design | straight |
| Type of locking | ONECLICK fast locking system |
| Pg screw connection | none |
| Material (Housing) | GD-Zn |
| Degree of protection (plugged in) | IP66/IP68 (2 m / 24 h) IP69K |

### Seal

| | |
|---|---|
| External cable diameter | 3 mm ... 15 mm (Universal gasket) |
| Seal material | FKM |


## Environmental and real-life conditions

### Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 105 °C (see to derating) |
| Permanent temperature | 125 °C (DIN EN 60512-9-2 / 1000 h) |


## Drawings

Schematic diagram




Connector pin assignment

Diagram




I = current strength, ϑ = ambient temperature, 6x 20 A

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1629188

**cUL Recognized**
Approval ID: E335019-20141210

**UL Recognized**
Approval ID: E335019-20141210

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC002635 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com