

HC-B 10-TMS/O2M32GS/O1M12S-EMV - Housing



1636554

<https://www.phoenixcontact.com/us/products/1636554>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sleeve housing, material: Die-cast aluminum, height: 100 mm

Commercial data

Item number	1636554
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF7AAA
GTIN	4017918984298
Weight per piece (including packing)	403.7 g
Weight per piece (excluding packing)	394.72 g
Country of origin	DE

1636554

<https://www.phoenixcontact.com/us/products/1636554>

Technical data

Product properties

Product type	Housing with screw locking
Housing type	Sleeve housing

Connection data

Tightening torque	3 Nm (Locking screw)
-------------------	----------------------

Dimensions

Width	57 mm
Height	100 mm
Length	92 mm

Installation dimensions

Length of the assembly cutout	32 mm
-------------------------------	-------

Material specifications

Seal material	NBR, conductive
Housing material	Die-cast aluminum
Housing surface material	EMC coating
Locking latch material	Stainless steel

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP68 (0.2 bar/24 h)
	IP69
Enclosure rating (NEMA)	4 (NEMA 250)
	4X (NEMA 250)
	6P (NEMA 250)
	NEMA 250

Mounting

Assembly note	In order to guarantee that the protective conductor contact functions even when plugged in at an angle, the two panel-mount flanges must have sufficient electrical contact with the metal mounting panel.
	To ensure optimum shielding, any insulating power coating must be removed from the profile gasket area on the control cabinet panel. Tightening torque of locking screw: 3 Nm.

HC-B 10-TMS/O2M32GS/O1M12S-EMV - Housing



1636554

<https://www.phoenixcontact.com/us/products/1636554>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1636554>



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-B 10-TMS/O2M32GS/O1M12S-EMV - Housing



1636554

<https://www.phoenixcontact.com/us/products/1636554>

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

ETIM

ETIM 10.0	EC000437
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

HC-B 10-TMS/O2M32GS/O1M12S-EMV - Housing



1636554

<https://www.phoenixcontact.com/us/products/1636554>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com