

FA MCR-FMR-22K-620-IP20-PT - Resistor network



1642820

<https://www.phoenixcontact.com/us/products/1642820>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Resistor network 22 k Ω parallel, 620 Ω in series for monitoring floating contacts and proximity switches. Line fault monitoring via isolation amplifiers or digital inputs in accordance with NAMUR IEC/EN 60947-5-6.

Commercial data

Item number	1642820
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C401
Product key	DK114Z
GTIN	4067923170063
Weight per piece (including packing)	6.9 g
Weight per piece (excluding packing)	5.6 g
Customs tariff number	85332100
Country of origin	US

Technical data

Product properties

Product type	Resistor network
Product family	Field Analog

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Supply

Voltage	≤ 12 V DC
Current	≤ 24 mA
Power consumption (Resistance)	0.3 W (parallel)
	0.5 W (In series)

Input data

Signal

Available input sources	floating switch contacts
-------------------------	--------------------------

Output data

Signal

Transmission Behavior	1:1 to the input signal + resistance values
Resistance	22 kΩ (parallel)
	620 Ω (In series)

Connection data

Connection method	Push-in spring connection
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ² (Ferrule without plastic sleeve)
	0.2 mm ² ... 0.75 mm ² (Ferrule with plastic sleeve)
Conductor cross-section AWG	24 ... 16
Pitch	3.5 mm

Dimensions

Width	35.1 mm
Height	14.2 mm
Depth	14.2 mm

Material specifications

Color	gray (RAL 7042)
-------	-----------------

1642820

<https://www.phoenixcontact.com/us/products/1642820>

Flammability rating according to UL 94	V0 (Housing)
Housing material	PA 6.6-FR

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 (not assessed by UL)
Ambient temperature (operation)	-40 °C ... 80 °C (Any mounting position)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Permissible humidity (operation)	0 % ... 95 % (non-condensing)

Altitude range (≤ 2000 m)

Altitude	≤ 2000 m
Ambient temperature (operation)	-40 °C ... 80 °C

Altitude range (≤ 3000 m)

Height range	≥ 2000 m ... 3000 m
Ambient temperature (operation)	-40 °C ... 72 °C

Altitude range (≤ 4000 m)

Height range	≥ 3000 m ... 4000 m
Ambient temperature (operation)	-40 °C ... 64 °C

Altitude range (≤ 5000 m)

Height range	≥ 4000 m ... 5000 m
Ambient temperature (operation)	-40 °C ... 56 °C

Approvals

CE

Certificate	CE-compliant
-------------	--------------

FA MCR-FMR-22K-620-IP20-PT - Resistor network



1642820

<https://www.phoenixcontact.com/us/products/1642820>

Classifications

ECLASS

ECLASS-13.0	27260114
ECLASS-15.0	27260114

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%