

ENLAR-M-KV-M25/M32 - Extension adapter



1647679

<https://www.phoenixcontact.com/us/products/1647679>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Extension adapter, connecting thread: M25 x 1.5, color: silver-colored, with O-ring



Product description

Extended from M25 to M32

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1647679 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BF68 |
| Product key | AF7DZX |
| GTIN | 4017918947088 |
| Weight per piece (including packing) | 28.8 g |
| Weight per piece (excluding packing) | 26.7 g |
| Customs tariff number | 74198090 |
| Country of origin | DE |

ENLAR-M-KV-M25/M32 - Extension adapter



1647679


<https://www.phoenixcontact.com/us/products/1647679>

Technical data

Product properties

| | |
|--------------|-------------------|
| Product type | Extension adapter |
|--------------|-------------------|

Dimensions

| | |
|----------------------------------|--|
| Dimensional drawing |  |
| Length | 21 mm |
| Length of the connecting thread | 6.5 mm |
| Length without connecting thread | 14.5 mm |
| Diameter Connecting thread | 25 mm |
| Connecting thread diameter | 25 mm |
| Hexagon angular dimension | 34 mm |
| Thread type connection side | M25 x 1.5 |
| Thread pitch | 1.5 mm |
| Thread type on seal side | M32 |

Material specifications

| | |
|----------------------|----------------------|
| Material | Brass, nickel-plated |
| Seal material O-ring | NBR |

Cable/line

| | |
|-------------------------|-------|
| External cable diameter | 20 mm |
| Halogen-free | no |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|---|
| Degree of protection | IP65 (Depends on the screw connection used) |
| Ambient temperature (operation) | -20 °C ... 80 °C |

Mounting

| | |
|---------------|---|
| Assembly note | With corresponding screw connection: IP68 |
|---------------|---|

ENLAR-M-KV-M25/M32 - Extension adapter


1647679

<https://www.phoenixcontact.com/us/products/1647679>



Drawings

Dimensional drawing



ENLAR-M-KV-M25/M32 - Extension adapter



1647679

<https://www.phoenixcontact.com/us/products/1647679>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27140806 |
| ECLASS-15.0 | 27140806 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000938 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31163000 |
|-------------|----------|

ENLAR-M-KV-M25/M32 - Extension adapter



1647679

<https://www.phoenixcontact.com/us/products/1647679>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | cf76fbee-a981-4975-9661-fad13641f423 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.612 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com