

# SAC-8P-10,0-PUR/P12FR - Sensor/actuator cable



1649245

<https://www.phoenixcontact.com/us/products/1649245>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 8-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket angled M12 Push Pull, coding: A, cable length: 10 m

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Save time, thanks to installation with push-pull fast locking

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1649245                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BF06                           |
| Product key                          | AF1CFA                         |
| GTIN                                 | 4067923181465                  |
| Weight per piece (including packing) | 22.22 g                        |
| Weight per piece (excluding packing) | 22.22 g                        |
| Customs tariff number                | 85444290                       |
| Country of origin                    | PL                             |

## Technical data

### Product properties

|                     |                       |
|---------------------|-----------------------|
| Product type        | Sensor/actuator cable |
| Application         | Standard              |
| Number of positions | 8                     |
| Shielded            | no                    |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications


|                                        |    |
|----------------------------------------|----|
| Flammability rating according to UL 94 | V0 |
|----------------------------------------|----|

### Electrical properties

|                       |         |
|-----------------------|---------|
| Nominal voltage $U_N$ | 30 V AC |
|                       | 30 V DC |
| Nominal current $I_N$ | 2 A     |

### Connector

#### Connection 1

|                             |                                                                                                                                                          |
|-----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Dimensional drawing         |  <p>Pin assignment M12 socket, 8-pos., A-coded, view female side</p> |
| Type                        | M12 Socket, angled, 8-position, Push Pull, Keying: A, Universal                                                                                          |
| Number of positions         | 8                                                                                                                                                        |
| Shielded                    | no                                                                                                                                                       |
| Signal type/category        | Universal                                                                                                                                                |
| Insertion/withdrawal cycles | ≥ 100                                                                                                                                                    |
| Insulation resistance       | ≥ 100 MΩ                                                                                                                                                 |
| Overvoltage category        | II                                                                                                                                                       |
| Degree of pollution         | 3                                                                                                                                                        |
| Material Contact            | CuZn                                                                                                                                                     |
| Material Contact surface    | Ni/Au                                                                                                                                                    |
| Material Contact carrier    | PA                                                                                                                                                       |
| Material Grip body          | TPU, hardly inflammable, self-extinguishing                                                                                                              |
| Material Seal               | FKM                                                                                                                                                      |
| Material Release            | Die-cast zinc, nickel-plated                                                                                                                             |

# SAC-8P-10,0-PUR/P12FR - Sensor/actuator cable



1649245

<https://www.phoenixcontact.com/us/products/1649245>

|                                        |                  |
|----------------------------------------|------------------|
| Flammability rating according to UL 94 | V0               |
| Degree of protection                   | IP65             |
|                                        | IP67             |
| Ambient temperature (operation)        | -25 °C ... 85 °C |
| Standard designation                   | M12 connector    |
| Standards/regulations                  | IEC 61076-2-010  |

## Connection 2

|                     |                             |
|---------------------|-----------------------------|
| Type                | Socket angled M12 Push Pull |
| Number of positions | 8                           |
| Locking type        | Push Pull                   |
| Coding type         | A                           |

## Cable/line

|              |      |
|--------------|------|
| Cable length | 10 m |
|--------------|------|

## PUR halogen-free black [PUR]

|                                 |                                                                                      |
|---------------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing             |  |
| Cable weight                    | 46 kg/km                                                                             |
| UL AWM Style                    | 20549 / 10493 (80°C/300 V)                                                           |
| Number of positions             | 8                                                                                    |
| Shielded                        | no                                                                                   |
| Cable type                      | PUR halogen-free black [PUR]                                                         |
| Conductor structure signal line | 32x 0.10 mm                                                                          |
| AWG signal line                 | 24                                                                                   |
| Conductor cross-section         | 8x 0.25 mm <sup>2</sup> (Signal line)                                                |
| Wire diameter incl. insulation  | 1.17 mm ±0.02 mm                                                                     |
| External cable diameter         | 5.90 mm ±0.15 mm                                                                     |
| Outer sheath, material          | PUR                                                                                  |
| External sheath, color          | black-gray RAL 7021                                                                  |
| Conductor material              | Bare Cu litz wires                                                                   |
| Material, filler                | PE                                                                                   |
| Material wire insulation        | PP                                                                                   |
| Single wire, color              | white, brown, green, yellow, gray, pink, blue, red                                   |
| Thickness, insulation           | ≥ 0.21 mm                                                                            |
| Thickness, outer sheath         | approx. 0.80 mm                                                                      |
| Overall twist                   | 8 wires around filler to the core                                                    |
| Max. conductor resistance       | ≤ 78 Ω/km (at 20 °C)                                                                 |

# SAC-8P-10,0-PUR/P12FR - Sensor/actuator cable



1649245

<https://www.phoenixcontact.com/us/products/1649245>

|                                               |                                                                                                                                        |
|-----------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| Insulation resistance                         | $\geq 1 \text{ G}\Omega \cdot \text{km}$ (at 20 °C)                                                                                    |
| Wave impedance                                | 100 $\Omega$ +15 % (with 1 MHz)                                                                                                        |
| Cable capacity                                | $\leq 70 \text{ pF/m}$                                                                                                                 |
| Nominal voltage, cable                        | $\leq 300 \text{ V}$                                                                                                                   |
| Test voltage                                  | $\geq 3000 \text{ V}$                                                                                                                  |
| Minimum bending radius, fixed installation    | 8 x D                                                                                                                                  |
| Minimum bending radius, flexible installation | 10 x D                                                                                                                                 |
| Smallest bending radius, fixed installation   | 48 mm                                                                                                                                  |
| Smallest bending radius, movable installation | 59 mm                                                                                                                                  |
| Dynamic load capacity (bending)               | Max. bending cycles: 10000000, Bending radius: 59 mm, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup> |
| Dynamic load capacity (torsion)               | Torsion: $\pm 180^\circ/\text{m}$ , Torsion cycles: $\geq 5000000$ , Torsional frequency: 35 cycles/min.                               |
| Halogen-free                                  | in accordance with DIN VDE 0472 part 815                                                                                               |
| Flame resistance                              | in accordance with UL 758/1581 FT2                                                                                                     |
| Resistance to oil                             | According to DIN EN 60332-2-2 (20 s)                                                                                                   |
| Other resistance                              | in accordance with DIN EN 60811-2-1                                                                                                    |
| Special properties                            | Highly resistant to acids, alkaline solutions and solvents                                                                             |
|                                               | hydrolysis and microbe resistant                                                                                                       |
|                                               | partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)                                                                           |
|                                               | Low adhesion                                                                                                                           |
|                                               | abrasion-resistant                                                                                                                     |
| Special properties                            | Flexible cable conduit capable                                                                                                         |
|                                               | Silicone-free                                                                                                                          |
|                                               | Free of substances which would hinder coating with paint or varnish                                                                    |
|                                               | flexible                                                                                                                               |
| Ambient temperature (operation)               | -40 °C ... 80 °C (cable, fixed installation)                                                                                           |
|                                               | -25 °C ... 80 °C (Cable, flexible installation)                                                                                        |

# SAC-8P-10,0-PUR/P12FR - Sensor/actuator cable


1649245

<https://www.phoenixcontact.com/us/products/1649245>



## Drawings

Dimensional drawing



M12 push-pull female connector, angled

Schematic diagram



Pin assignment M12 socket, 8-pos., A-coded, view female side

# SAC-8P-10,0-PUR/P12FR - Sensor/actuator cable



1649245

<https://www.phoenixcontact.com/us/products/1649245>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

# SAC-8P-10,0-PUR/P12FR - Sensor/actuator cable



1649245

<https://www.phoenixcontact.com/us/products/1649245>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)