

VS-09-PROFIBUS-SC - D-SUB connector



1654549

<https://www.phoenixcontact.com/us/products/1654549>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB connector, degree of protection: IP67, number of positions: 9, material: Plastic, connection method: Screw connection, connection cross section: AWG 26- 16, cable outlet: angled, with integrated termination resistor, housing size: 1, color: gray, PROFIBUS



Your advantages

- EMC protection
- Switchable termination resistor
- Coding sections (CR) as protection against mismatching

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1654549 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB19 |
| Product key | ABNCBA |
| GTIN | 4017918955083 |
| Weight per piece (including packing) | 93 g |
| Weight per piece (excluding packing) | 93 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

Technical data

Notes

Safety note

| | |
|--------------------|--|
| <p>Safety note</p> | <p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p> <ul style="list-style-type: none"> • WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible. • WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product. • The products are suitable for applications in plant, controller, and electrical device engineering. • When operating the connectors in outdoor applications, they must be separately protected against environmental influences. • Assembled products may not be manipulated or improperly opened. • Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products). • When using the product in direct connection with third-party manufacturers, the user is responsible. • For operating voltages > 50 V AC, conductive connector housings must be grounded • Only use tools recommended by Phoenix Contact • The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product. • Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at phoenixcontact.com/products • Operate the connector only when it is fully plugged in and interlocked. • Operate the connector only when it is fully plugged in. • Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards. • Observe the minimum bending radius of the cable. Lay the cable without twisting it. • VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector |
|--------------------|--|

Product properties

VS-09-PROFIBUS-SC - D-SUB connector



1654549

<https://www.phoenixcontact.com/us/products/1654549>

| | |
|----------------------|-----------------------------|
| Product type | Data connector (cable side) |
| Application | PROFIBUS |
| Type | D-SUB |
| Number of positions | 9 |
| No. of cable outlets | 2 |
| Shielded | yes |
| Cable outlet | angled |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 2 |

Electrical properties

| | |
|-----------------------|--------|
| Rated voltage (III/3) | 50 V |
| Rated surge voltage | 0.5 kV |
| Rated current | 1 A |
| Transmission medium | Copper |

Connection data

Connection technology

| | |
|------------------------------|---|
| Connection method | Screw connection |
| Connection cross section AWG | 26 ... 16 (solid) |
| | 26 ... 18 (flexible) |
| Conductor cross-section | 0.14 mm ² ... 1.5 mm ² (solid) |
| | 0.14 mm ² ... 1 mm ² (flexible) |

Interfaces

| | |
|----------------------|----------|
| Signal type/category | PROFIBUS |
|----------------------|----------|

Dimensions

| | |
|--------|--------|
| Width | 24 mm |
| Height | 59 mm |
| Length | 107 mm |

Material specifications

| | |
|--|----------------|
| Color | gray |
| Flammability rating according to UL 94 | V0 |
| Housing material | Plastic |
| Housing surface material | PA, light gray |
| Cable seal material | CR/NBR |

Cable/line

| | |
|---|---------------|
| Signal type/category | PROFIBUS |
| External cable diameter | 5 mm ... 9 mm |
| Stripping length of the individual wire | 7 mm |

VS-09-PROFIBUS-SC - D-SUB connector



1654549

<https://www.phoenixcontact.com/us/products/1654549>

| | |
|---------------------|---------------------|
| Cable cross section | 0.2 mm ² |
|---------------------|---------------------|

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 200 |
|-----------------------------|-------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Degree of protection | IP67 |
| | IP67 |
| Ambient temperature (operation) | -20 °C ... 75 °C |

VS-09-PROFIBUS-SC - D-SUB connector



1654549

<https://www.phoenixcontact.com/us/products/1654549>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440290 |
| ECLASS-15.0 | 27440322 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001132 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

VS-09-PROFIBUS-SC - D-SUB connector



1654549

<https://www.phoenixcontact.com/us/products/1654549>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 8acc620f-7915-4086-a0a4-b948cd93d2b0 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 2.016 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com