

VS-SCRJ-HCS-FA-IP20 - FO connectors



1654866

<https://www.phoenixcontact.com/us/products/1654866>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



FO connectors, degree of protection: IP20, number of positions: 2, MM, material: Plastic, connection method: Cable connection, cable outlet: straight, color: black

SC-RJ

Your advantages

- Suitable for quick and easy field assembly or repair
- Flexible application, thanks to reusable connector
- Outstanding transmission properties
- Ideal for PCF step-index (SI) fibers
- Compact design, thanks to SC-RJ pin connector pattern
- No bonding or polishing

Commercial data

Item number	1654866
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIAB
GTIN	4046356028837
Weight per piece (including packing)	21.5 g
Weight per piece (excluding packing)	21.5 g
Customs tariff number	85367000
Country of origin	DE

VS-SCRJ-HCS-FA-IP20 - FO connectors



1654866

<https://www.phoenixcontact.com/us/products/1654866>

Technical data

Notes

Order information:	Set packaging: please order 2313070
--------------------	-------------------------------------

Product properties

Product type	Fiber optic connector (cable side)
Application	neutral
Type	SC-RJ
Number of positions	2
Connection profile	SCRJ
Set comprises	2313070 PSM-SET-SCRJ-DUP/2-HCS
No. of cable outlets	2
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Attenuation	≥ 2 dB (Insertion attenuation)
Transmission medium	FO
Transmission characteristics (category)	MM

Connection data

Connection method	Cable connection
-------------------	------------------

Dimensions

Width	16.5 mm
Height	11 mm
Length	88.5 mm

Mechanical characteristics

Ferrule diameter	2.50 mm
------------------	---------

Material specifications

Color	black
Material	Plastic
Flammability rating according to UL 94	V0
Ferrule material	Copper alloy
Housing material	Plastic

Cable/line

Cable type	PCF 200/230
Cable type	Single wires

VS-SCRJ-HCS-FA-IP20 - FO connectors



1654866

<https://www.phoenixcontact.com/us/products/1654866>

External cable diameter	2.9 mm ... 2.9 mm
Individual wire diameter	2.9 mm

FO cable

Fiber	200/230 μm
Fiber type	PCF
Attenuation	≤ 1.5 dB
Transmission medium	FO

Characteristics

Attenuation	≥ 2 dB (Insertion attenuation)
-------------	-------------------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20 IP20
Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Ambient temperature (assembly)	0 °C ... 50 °C

Mounting

Mounting type	For field assembly
cable layer type	Indoors

Drawings

Schematic diagram



VS-SCRJ-HCS-FA-IP20 - FO connectors



1654866

<https://www.phoenixcontact.com/us/products/1654866>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1654866>



UL Listed

Approval ID: E308814-20070105

VS-SCRJ-HCS-FA-IP20 - FO connectors



1654866

<https://www.phoenixcontact.com/us/products/1654866>

Classifications

ECLASS

ECLASS-13.0	19170122
ECLASS-15.0	19170122

ETIM

ETIM 10.0	EC001122
-----------	----------

UNSPSC

UNSPSC 21.0	43223300
-------------	----------

VS-SCRJ-HCS-FA-IP20 - FO connectors



1654866

<https://www.phoenixcontact.com/us/products/1654866>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	1.281 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com