

# VS-09-BU-DSUB-HD-CD-B - D-SUB contact support



1655124

<https://www.phoenixcontact.com/us/products/1655124>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact carrier, shell size 1, for 15 signal contacts, type of contact socket, for crimp contacts, straight, fixing with a 3 mm hole, for panel mounting frame and sleeve housing VS-09-..



## Your advantages

- Compatible with IP67 sleeve housing and panel-mount frame
- Easy assembly

## Commercial data

Item number	1655124
Packing unit	100 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAB
GTIN	4046356029063
Weight per piece (including packing)	9.61 g
Weight per piece (excluding packing)	4.45 g
Customs tariff number	85366990
Country of origin	DE

1655124

<https://www.phoenixcontact.com/us/products/1655124>

## Technical data

### Product properties

Product type	Contact insert
Application	high-position
Type	D-SUB
Number of positions	15
Connection profile	D-SUB
Number of slots	1
Shielded	yes

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Rated voltage (III/3)	60 V
Rated surge voltage	1 kV
Rated current	3 A (at 20 °C)
Test voltage	1000 V
Transmission medium	Copper

### Connection data

Connection method	Crimp connection
-------------------	------------------

### Dimensions

Width	16.1 mm
Height	12.93 mm
Length	31.19 mm

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated
Contact surface material	Gold
Contact carrier material	Glass-fiber reinforced thermoplastics, UL 94 V0

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

### Environmental and real-life conditions

#### Ambient conditions

# VS-09-BU-DSUB-HD-CD-B - D-SUB contact support



1655124

<https://www.phoenixcontact.com/us/products/1655124>

Degree of protection	IP20
Ambient temperature (operation)	-55 °C ... 115 °C

## Mounting

Mounting type	Screw mounting
---------------	----------------

1655124

<https://www.phoenixcontact.com/us/products/1655124>

## Classifications

### ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

### ETIM

ETIM 10.0	EC001132
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1655124

<https://www.phoenixcontact.com/us/products/1655124>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.137 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)