

VS-09-BU-DSUB-HD-CD-B - D-SUB contact support



1655124

<https://www.phoenixcontact.com/us/products/1655124>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact carrier, shell size 1, for 15 signal contacts, type of contact socket, for crimp contacts, straight, fixing with a 3 mm hole, for panel mounting frame and sleeve housing VS-09-..



Your advantages

- Compatible with IP67 sleeve housing and panel-mount frame
- Easy assembly

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1655124 |
| Packing unit | 100 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB19 |
| Product key | ABNCAB |
| GTIN | 4046356029063 |
| Weight per piece (including packing) | 9.61 g |
| Weight per piece (excluding packing) | 4.45 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

1655124

<https://www.phoenixcontact.com/us/products/1655124>

Technical data

Product properties

| | |
|---------------------|----------------|
| Product type | Contact insert |
| Application | high-position |
| Type | D-SUB |
| Number of positions | 15 |
| Connection profile | D-SUB |
| Number of slots | 1 |
| Shielded | yes |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 2 |

Electrical properties

| | |
|-----------------------|----------------|
| Rated voltage (III/3) | 60 V |
| Rated surge voltage | 1 kV |
| Rated current | 3 A (at 20 °C) |
| Test voltage | 1000 V |
| Transmission medium | Copper |

Connection data

| | |
|-------------------|------------------|
| Connection method | Crimp connection |
|-------------------|------------------|

Dimensions

| | |
|--------|----------|
| Width | 16.1 mm |
| Height | 12.93 mm |
| Length | 31.19 mm |

Material specifications

| | |
|--|---|
| Flammability rating according to UL 94 | V0 |
| Housing material | Metal |
| Housing surface material | metal-plated |
| Contact surface material | Gold |
| Contact carrier material | Glass-fiber reinforced thermoplastics, UL 94 V0 |

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 500 |
|-----------------------------|-------|

Environmental and real-life conditions

Ambient conditions

VS-09-BU-DSUB-HD-CD-B - D-SUB contact support



1655124

<https://www.phoenixcontact.com/us/products/1655124>

| | |
|---------------------------------|-------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -55 °C ... 115 °C |

Mounting

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

1655124

<https://www.phoenixcontact.com/us/products/1655124>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440302 |
| ECLASS-15.0 | 27440323 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001132 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

1655124

<https://www.phoenixcontact.com/us/products/1655124>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.137 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com