VS-09-A-EMV-S - D-SUB EMC shroud

1688463

https://www.phoenixcontact.com/us/products/1688463

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB EMC shroud, for panel mounting frame VS-09-..., shell size 1, shielded



Commercial data

Item number	1688463
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	AB19
Product key	ABNCBZ
GTIN	4017918818395
Weight per piece (including packing)	0.816 g
Weight per piece (excluding packing)	0.75 g
Customs tariff number	85389099
Country of origin	CZ

Technical data

Product properties

Product type	Shroud
Application	Shroud
Type	09

Insulation characteristics

Degree of pollution	2

Dimensions

Width	35.9 mm
Height	17.5 mm

Material specifications

Color	Bare metallic
Material	Metal
Housing material	Nickel silver

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 1000

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C

Classifications

ECLASS

ECLASS-13.0	27440392
ECLASS-15.0	27440392

ETIM

ETIM 10.0	EC002943

UNSPSC

UNSPSC 21.0	43222600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.246 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com