

# VS-09-GC-BU/BU - D-SUB gender changer



1688722

<https://www.phoenixcontact.com/us/products/1688722>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB gender changer, degree of protection: IP20, number of positions: 9, material: Metal, connection method: Coupling, cable outlet: angled, housing size: 1, Universal



## Commercial data

Item number	1688722
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB19
Product key	ABNCAB
GTIN	4017918942632
Weight per piece (including packing)	10.89 g
Weight per piece (excluding packing)	10.89 g
Customs tariff number	85366990
Country of origin	DE

1688722

<https://www.phoenixcontact.com/us/products/1688722>

## Technical data

### Product properties

Product type	Contact insert
Type	D-SUB
Number of positions	9
Shielded	no
Cable outlet	angled

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Rated voltage (III/3)	125 V
Rated surge voltage	1 kV
Rated current	5 A
Transmission medium	Copper

### Connection data

Connection method	Coupling
-------------------	----------

### Interfaces

Signal type/category	Universal
----------------------	-----------

### Dimensions

Width	17.6 mm
Height	30.86 mm
Length	12.5 mm

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Contact material	Copper alloy
Contact surface material	Hard gold-plated over nickel
Contact carrier material	Polyester GF

### Cable/line

Signal type/category	Universal
----------------------	-----------

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 200
-----------------------------	-------

# VS-09-GC-BU/BU - D-SUB gender changer



1688722

<https://www.phoenixcontact.com/us/products/1688722>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-55 °C ... 125 °C

## Mounting

Mounting type	Threads
---------------	---------

# VS-09-GC-BU/BU - D-SUB gender changer



1688722

<https://www.phoenixcontact.com/us/products/1688722>

## Classifications

### ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440325

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1688722

<https://www.phoenixcontact.com/us/products/1688722>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.2 kg CO2e
---------	-------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)