

# VS-15-ST-DSUB-HD-CD-B - D-SUB contact support



1655195

<https://www.phoenixcontact.com/us/products/1655195>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact carrier, shell size 2, for 26 signal contacts, type of contact pin, for crimp contacts, straight, fixing with a 3 mm hole, for panel mounting frame and sleeve housing VS-15-...



## Your advantages

- Compatible with IP67 sleeve housing and panel-mount frame
- Easy assembly

## Commercial data

Item number	1655195
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB19
Product key	ABNCAA
GTIN	4046356029131
Weight per piece (including packing)	11.18 g
Weight per piece (excluding packing)	5.52 g
Customs tariff number	85366990
Country of origin	DE

# VS-15-ST-DSUB-HD-CD-B - D-SUB contact support



1655195

<https://www.phoenixcontact.com/us/products/1655195>

## Technical data

### Product properties

Product type	Male insert
Application	high-position
Type	D-SUB
Number of positions	26
Connection profile	D-SUB 15
Shielded	no

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2


### Electrical properties

Rated voltage (III/3)	60 V
Rated surge voltage	1 kV
Rated current	3 A (at 20 °C)
Test voltage	1000 V
Transmission medium	Copper

### Connection data

Connection method	Crimp connection
-------------------	------------------

### Dimensions

Dimensional drawing	
Width	16 mm
Height	12.93 mm
Length	39.52 mm

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Steel, tin-plated
Contact material	Copper alloy
Contact carrier material	Glass-fiber reinforced thermoplastics, UL 94 V0

### Mechanical properties

#### Mechanical data

# VS-15-ST-DSUB-HD-CD-B - D-SUB contact support



1655195

<https://www.phoenixcontact.com/us/products/1655195>

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-55 °C ... 115 °C
---------------------------------	-------------------

## Mounting

Mounting type	Hole
---------------	------


# VS-15-ST-DSUB-HD-CD-B - D-SUB contact support



1655195

<https://www.phoenixcontact.com/us/products/1655195>

## Drawings



D-SUB contact carrier

1655195

<https://www.phoenixcontact.com/us/products/1655195>

## Classifications

### ECLASS

ECLASS-13.0

27440214

### ETIM

ETIM 9.0

EC001132

### UNSPSC

UNSPSC 21.0

39121400

# VS-15-ST-DSUB-HD-CD-B - D-SUB contact support



1655195

<https://www.phoenixcontact.com/us/products/1655195>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)