


VS-09-BU-DSUB/CAN - D-SUB contact insert

1689051

<https://www.phoenixcontact.com/us/products/1689051>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB CAN-BUS contact insert, type 09, version: Socket



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1689051 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Note | Made to order (non-returnable) |
| Sales key | AB12 |
| Product key | ABNCAB |
| GTIN | 4017918876814 |
| Weight per piece (including packing) | 11.92 g |
| Weight per piece (excluding packing) | 10.678 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

VS-09-BU-DSUB/CAN - D-SUB contact insert



1689051

<https://www.phoenixcontact.com/us/products/1689051>

Technical data

Product properties

| | |
|--------------------|----------------|
| Product type | Contact insert |
| Type | D-SUB |
| Connection profile | D-SUB |
| Number of slots | 1 |
| Shielded | yes |

Electrical properties

| | |
|---------------------|--------|
| Transmission medium | Copper |
| Power transmission | Power |

Connection data

| | |
|-------------------|------------------|
| Connection method | Screw connection |
|-------------------|------------------|

Dimensions

| | |
|--------|-----------|
| Width | 24 mm |
| Height | 59.8 mm |
| Length | 104.65 mm |

Material specifications

| | |
|--|--------------|
| Flammability rating according to UL 94 | V0 |
| Contact material | Copper alloy |
| Contact surface material | tin-plated |
| Contact carrier material | PA |

Environmental and real-life conditions

Ambient conditions

| | |
|----------------------|------|
| Degree of protection | IP20 |
|----------------------|------|

Mounting

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

VS-09-BU-DSUB/CAN - D-SUB contact insert



1689051

<https://www.phoenixcontact.com/us/products/1689051>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440302 |
| ECLASS-15.0 | 27440323 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001132 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

VS-09-BU-DSUB/CAN - D-SUB contact insert



1689051

<https://www.phoenixcontact.com/us/products/1689051>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 45e6f9ad-136b-4f7e-b508-66f984537c0c |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 3.277 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com