

VS-SCRJ-POF-FA-IP67 - FO connectors



1657009

<https://www.phoenixcontact.com/us/products/1657009>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



FO connectors, degree of protection: IP67, number of positions: 2, MM, material: Plastic, cable outlet: straight, color: gray

Commercial data

Item number	1657009
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB17
Product key	ABNNBA
GTIN	4046356081382
Weight per piece (including packing)	39.6 g
Weight per piece (excluding packing)	32.234 g
Customs tariff number	85367000
Country of origin	DE

VS-SCRJ-POF-FA-IP67 - FO connectors



1657009

<https://www.phoenixcontact.com/us/products/1657009>

Technical data

Product properties

Product type	Fiber optic connector (cable side)
Application	neutral
Type	SC-RJ
Number of positions	2
Connection profile	SCRJ
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Attenuation	≤ 1.5 dB (Insertion attenuation)
Transmission medium	FO
Transmission characteristics (category)	MM

Dimensions

Width	38.4 mm
Height	22.8 mm
Length	125 mm

Mechanical characteristics

Ferrule diameter	2.50 mm
------------------	---------

Material specifications

Color	gray
Material	Plastic
Flammability rating according to UL 94	V0
Ferrule material	Copper alloy
Housing material	Plastic
Cable seal material	NBR
O-ring material	FPM

Cable/line

External cable diameter	5 mm ... 8.5 mm
Wire diameter	2.2 mm

FO cable

Fiber type	POF fiber A4A
------------	---------------

Mechanical properties

Mechanical data

VS-SCRJ-POF-FA-IP67 - FO connectors



1657009

<https://www.phoenixcontact.com/us/products/1657009>

Insertion/withdrawal cycles	≥ 1000
-----------------------------	--------

Characteristics

Attenuation	≤ 1.5 dB (Insertion attenuation)
-------------	----------------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 70 °C

VS-SCRJ-POF-FA-IP67 - FO connectors



1657009

<https://www.phoenixcontact.com/us/products/1657009>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1657009>



UL Listed

Approval ID: E308814-20070105

VS-SCRJ-POF-FA-IP67 - FO connectors



1657009

<https://www.phoenixcontact.com/us/products/1657009>

Classifications

ECLASS

ECLASS-13.0	19170122
ECLASS-15.0	19170122

ETIM

ETIM 10.0	EC001122
-----------	----------

UNSPSC

UNSPSC 21.0	43223300
-------------	----------

1657009

<https://www.phoenixcontact.com/us/products/1657009>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1)
SCIP	b2e1cf66-8c8e-4dad-bf32-d54d711cd2cd

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com