

CK1,6-ED-2,50ST AG - Crimp contact



1663381

<https://www.phoenixcontact.com/us/products/1663381>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, series: HC-M-12, Pin, turned, contact diameter: 1.6 mm, rated current: 10 A, connection cross section: 2.5 mm² ... 2.5 mm², AWG 14...14, contact material: Cu alloy

Commercial data

Item number	1663381
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF65
Product key	AF7AIA
GTIN	4017918123192
Weight per piece (including packing)	0.684 g
Weight per piece (excluding packing)	0.65 g
Customs tariff number	85366990
Country of origin	DE

CK1,6-ED-2,50ST AG - Crimp contact



1663381

<https://www.phoenixcontact.com/us/products/1663381>

Technical data

Product properties

Product type	Crimp contact
Series	HC-M-12
	HC-M-EMV
	HC-D
	HC-DD
	VC-D
	HC-M-03/04
	HC-M-17
	HC-K
	HC-Q
	HC-COM
HC-M-42	
Contact material type	turned

Connection data

Connection technology

Contact connection type	Pin
Connection method	Crimp connection


Conductor connection

Stripping length	6 mm
Connection cross section	2.5 mm ² ... 2.5 mm ²
Connection cross section AWG	14 ... 14

Material specifications

Material Contact	Cu alloy
Material Contact surface	Ag

Dimensions

Dimensional drawing	
Diameter (Contact diameter)	1.6 mm

Electrical properties

Rated current	10 A (Take into account the derating of the contact insert used. The rated current corresponds to the maximum possible connection cross-section.)
---------------	---

Mechanical properties

CK1,6-ED-2,50ST AG - Crimp contact



1663381

<https://www.phoenixcontact.com/us/products/1663381>

Mechanical data

Insertion/withdrawal cycles

≥ 500

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)

-40 °C ... 125 °C

CK1,6-ED-2,50ST AG - Crimp contact




1663381

<https://www.phoenixcontact.com/us/products/1663381>

Drawings

Dimensional drawing



Dimensional drawing

CK1,6-ED-2,50ST AG - Crimp contact



1663381

<https://www.phoenixcontact.com/us/products/1663381>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1663381>



EAC

Approval ID: RU C-DE.AI30.B.01102

CK1,6-ED-2,50ST AG - Crimp contact



1663381

<https://www.phoenixcontact.com/us/products/1663381>

Classifications

ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

ETIM

ETIM 10.0	EC000796
-----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK1,6-ED-2,50ST AG - Crimp contact



1663381

<https://www.phoenixcontact.com/us/products/1663381>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com