

SAC-5P-M12FR/ 8,0-PUR/M12FR VW - Sensor/actuator cable



1693869

<https://www.phoenixcontact.com/us/products/1693869>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, PUR halogen-free, irradiated, orange RAL 2003, Socket angled M12, coding: A, on Socket angled M12, coding: A, cable length: 8 m

Commercial data

Item number	1693869
Packing unit	5 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	02
Product key	AF1CDA
GTIN	4017918481810
Weight per piece (including packing)	347.92 g
Weight per piece (excluding packing)	339.36 g
Country of origin	PL

SAC-5P-M12FR/ 8,0-PUR/M12FR VW - Sensor/actuator cable



1693869

<https://www.phoenixcontact.com/us/products/1693869>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	5
No. of cable outlets	1
Shielded	no
Coding	A

Material specifications

Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU

Electrical properties

Rated voltage in acc. with IEC 61076-2-101	60 V
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display present	no
------------------------	----

Connector

Connection 1

Type	Socket angled M12
Number of positions	5
Coding type	A

Connection 2

Type	Socket angled M12
Number of positions	5
Coding type	A

Cable/line

Cable length	8 m
--------------	-----

PUR irradiated halogen-free orange [150]

SAC-5P-M12FR/ 8,0-PUR/M12FR VW - Sensor/actuator cable



1693869

<https://www.phoenixcontact.com/us/products/1693869>

Dimensional drawing	
Number of positions	5
Shielded	no
Cable type	PUR irradiated halogen-free orange [150]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor structure, voltage supply	24x 0.15 mm
AWG power supply	20
Conductor cross-section	4x 0.34 mm ² (Signal line) 1x 0.5 mm ² (PE connection)
External cable diameter	5.20 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	orange RAL 2003
Conductor material	Bare Cu litz wires
Material wire insulation	PE
Single wire, color	brown, white, blue, black, green-yellow
Overall twist	5 cores, twisted
Max. conductor resistance	≤ 57.5 Ω/km (with 0.34 mm ² conductor cross-section) ≤ 39 Ω/km (with 0.5 mm ² conductor cross-section)
Nominal voltage, cable	250 V (AC)
Test voltage	2000 V (50 Hz, 5 minutes)
Smallest bending radius, fixed installation	20 mm
Smallest bending radius, movable installation	30 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 52 mm, Traversing path: 10 m, Traversing rate: 3 m/s
Halogen-free	The cable is halogen-free
Flame resistance	DIN VDE 0472 part 804, test type B
Other resistance	hydrolysis and microbe resistant UV resistant Resistant to welding splashes
Special properties	Silicone-free Irradiated
Ambient temperature (operation)	-50 °C ... 105 °C (cable, fixed installation) -40 °C ... 105 °C (Cable, flexible installation)

Environmental and real-life conditions

SAC-5P-M12FR/ 8,0-PUR/M12FR VW - Sensor/actuator cable



1693869

<https://www.phoenixcontact.com/us/products/1693869>

Ambient conditions

Ambient temperature (operation) (male connector/female connector)	-25 °C ... 90 °C (Plug / socket)
Ambient temperature (operation) (Cable, fixed installation)	-50 °C ... 105 °C (cable, fixed installation)
Ambient temperature (operation) (flexible installation)	-40 °C ... 105 °C (Cable, flexible installation)


SAC-5P-M12FR/ 8,0-PUR/M12FR VW - Sensor/actuator cable

1693869

<https://www.phoenixcontact.com/us/products/1693869>


Drawings

Dimensional drawing



M12 x 1 socket, angled

Dimensional drawing




M12 x 1 socket, angled

SAC-5P-M12FR/ 8,0-PUR/M12FR VW - Sensor/actuator cable

1693869


<https://www.phoenixcontact.com/us/products/1693869>

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

SAC-5P-M12FR/ 8,0-PUR/M12FR VW - Sensor/actuator cable



1693869

<https://www.phoenixcontact.com/us/products/1693869>

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

SAC-5P-M12FR/ 8,0-PUR/M12FR VW - Sensor/actuator cable



1693869

<https://www.phoenixcontact.com/us/products/1693869>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1693869>

	 UL Listed Approval ID: FILE E 221474			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	4 A	-	-

	 cUL Listed Approval ID: FILE E 221474			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	4 A	-	-

 EAC-RoHS Approval ID: RU D-DE.HB35.B.00387	
--	--

SAC-5P-M12FR/ 8,0-PUR/M12FR VW - Sensor/actuator cable



1693869

<https://www.phoenixcontact.com/us/products/1693869>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-M12FR/ 8,0-PUR/M12FR VW - Sensor/actuator cable



1693869

<https://www.phoenixcontact.com/us/products/1693869>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	9.104 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com