

PLD E 708 W 400 MS/E - LED enclosure light



1694093

<https://www.phoenixcontact.com/us/products/1694093>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

LED enclosure light, AC wide range input, color temperature 5000 K, with motion detector, type E socket (e.g., for France and Belgium)



Product description

The LED light is designed to illuminate the interior of control cabinets. The integrated optics ensure optimum illumination of the control cabinet. Depending on the requirements, the light can be equipped with mounting elements for screw or snap-in mounting at two positions. The mounting elements are supplied as standard. Mounting with magnets is also possible. The magnets are available as accessories. You can connect several lights in succession. You can control the light mode via a switch. You can switch the light on or off permanently or enable automatic mode. In automatic mode, the light is switched on and off via an integrated motion detector.

Your advantages

- Optimum illumination of the control cabinet thanks to glare-free optics
- Integrated motion detector
- Socket enables the operation of external devices
- AC wide-range input
- Optical power 1400 lm
- Color temperature 5000 K (neutral white)

Commercial data

Item number	1694093
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR08
Product key	DRL235
GTIN	4067923256064
Weight per piece (including packing)	587.7 g
Weight per piece (excluding packing)	470 g
Customs tariff number	94054231
Country of origin	DE

PLD E 708 W 400 MS/E - LED enclosure light



1694093

<https://www.phoenixcontact.com/us/products/1694093>

Technical data

Product properties

Product type	Enclosure light
Application	Control cabinet
Mounting position	any
For country-specific use in	France
	Belgium
	Poland
Special properties	can be switched in series
	including mounting accessories
Socket type	Type E
Light color	Neutral white

Electrical properties

Supply: Module electronics

Supply voltage range	100 V AC ... 240 V AC (50/60 Hz)
Current consumption	max. 16 A (from the socket)
Power consumption	11 W (LEDs)

Signaling

Motion detector

Detection range	max. 1.8 m
Detection angle	87 °
Lighting duration	180 s (Retriggered)

Light properties

Source of light type	LED
Number of LEDs	32
Color temperature	5000 K
Color rendering index	84
Luminous flux	1400 lm (Net luminous flux)
Illumination	max. 5920 lx (Along the optical axis, distance: 50 cm)
	max. 1480 lx (Along the optical axis, distance: 1 m)
Ordinance	Delegated Regulation (EU) 2019/2015
Energy efficiency class	C (1 light source)
Note	This product contains an energy efficiency class C light source.

Dimensions

Width	77 mm
Height	55 mm
Length	341 mm

PLD E 708 W 400 MS/E - LED enclosure light



1694093

<https://www.phoenixcontact.com/us/products/1694093>

Material specifications

Color (Housing)	black (RAL 9005)
Material	PC-ABS (Housing)
	highly transparent polycarbonate (Visual appearance)
Housing material	Plastic

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 2000 m above sea level)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 85 % (non-condensing)

Energy labeling

Ordinance	Delegated Regulation (EU) 2019/2015
Note (EPREL)	The EPREL entry can be searched for with the registration number (https://eprel.ec.europa.eu/screen/home)
	The EPREL entry can be searched for with the model ID (https://eprel.ec.europa.eu/screen/product/lightsources)

Energy labeling (Light source 1)

Registration number	2192509
Model ID	79 LMX PMB
Energy efficiency class	C
Number of light sources	1

Mounting

Mounting type	Screw mounting
	Snap-on assembly
Assembly note	Magnet attachment available as an accessory
Mounting position	any

PLD E 708 W 400 MS/E - LED enclosure light


1694093

<https://www.phoenixcontact.com/us/products/1694093>



Drawings

Schematic diagram



Type E socket


PLD E 708 W 400 MS/E - LED enclosure light

1694093

<https://www.phoenixcontact.com/us/products/1694093>



Schematic diagram



Pin assignment

PLD E 708 W 400 MS/E - LED enclosure light



1694093

<https://www.phoenixcontact.com/us/products/1694093>

Classifications

ECLASS

ECLASS-13.0	27182808
ECLASS-15.0	27182808

ETIM

ETIM 10.0	EC000321
-----------	----------

UNSPSC

UNSPSC 21.0	32151500
-------------	----------

PLD E 708 W 400 MS/E - LED enclosure light



1694093

<https://www.phoenixcontact.com/us/products/1694093>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com