

# SACC-DSIV-M12MS-5CON-L 90 - Device connector rear mounting



1694224

<https://www.phoenixcontact.com/us/products/1694224>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device connector rear mounting, 5-position, Pin, angled, M12, A-coding, Wave soldering



## Commercial data

Item number	1694224
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AB23
Product key	ABQEGI
GTIN	4017918177508
Weight per piece (including packing)	12.03 g
Weight per piece (excluding packing)	11.64 g
Customs tariff number	85366990
Country of origin	HU

# SACC-DSIV-M12MS-5CON-L 90 - Device connector rear mounting



1694224

<https://www.phoenixcontact.com/us/products/1694224>

## Technical data

### Mounting

Mounting type	Rear mounting (M12 x 1, with locking nut)
---------------	---

### Product properties

Product type	Circular connectors (device side)
Number of positions	5
Shielded	no
Coding	A
Thread type	M12

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Material Housing	CuZn
Material Housing surface	Ni
Material Contact carrier	PA 6.6
Material Contact	CuZn
Material Contact surface	Au
Material Seal	NBR
Flammability rating according to UL 94	HB

### Electrical properties

Contact resistance	$\leq 5 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	60 V
Nominal current $I_N$	4 A

### Connection data

#### Conductor connection

Connection method	Wave soldering
Contact connection type	Pin

### Connector

#### Connection 1

Head design	Pin
Head cable outlet	angled
Head thread type	M12
Coding	A

# SACC-DSIV-M12MS-5CON-L 90 - Device connector rear mounting



1694224

<https://www.phoenixcontact.com/us/products/1694224>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C
UL Type Rating	Type 4 (indoor use only)

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

# SACC-DSIV-M12MS-5CON-L 90 - Device connector rear mounting

1694224

<https://www.phoenixcontact.com/us/products/1694224>

## Drawings

Schematic diagram



Pin assignment M12 male connector, 5-pos., A-coded, male side

# SACC-DSIV-M12MS-5CON-L 90 - Device connector rear mounting



1694224

<https://www.phoenixcontact.com/us/products/1694224>


## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1694224>

 <b>cUL Recognized</b> Approval ID: FILE E 221474				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
	60 V	4 A	-	-

 <b>UL Recognized</b> Approval ID: FILE E 221474				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
	60 V	4 A	-	-

 <b>UL Recognized</b> Approval ID: E221474-20070307				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
	60 V	4 A	-	-

 <b>cUL Recognized</b> Approval ID: E221474-20070307				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
	60 V	4 A	-	-

# SACC-DSIV-M12MS-5CON-L 90 - Device connector rear mounting



1694224

<https://www.phoenixcontact.com/us/products/1694224>

## Classifications

### ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

### ETIM

ETIM 10.0	EC003568
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-DSIV-M12MS-5CON-L 90 - Device connector rear mounting



1694224

<https://www.phoenixcontact.com/us/products/1694224>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	56fb8f13-4363-4a90-bfec-025ff82832b5

### EF3.1 Climate Change

CO2e kg	0.669 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)