

TGGM/CDIO/17-BU - Cable connector



1667905

<https://www.phoenixcontact.com/us/products/1667905>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 17-pos. product version without external cable gland

M23, Cable connector, application: Signal, series: UC, shielded: yes, Screw locking mechanism, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Socket, Crimp connection, coding: N. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1667905
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAIA
GTIN	4017918163600
Weight per piece (including packing)	152.2 g
Weight per piece (excluding packing)	143.319 g
Customs tariff number	85366990
Country of origin	DE

1667905

<https://www.phoenixcontact.com/us/products/1667905>

Technical data

Product properties

Product type	Circular connector (cable-side)
Number of positions	17

Material specifications

Seal material	NBR
---------------	-----

Connector

Insulating body

Note	Assembly note Integrated contacts: 17 x 1599600
Coding	N
Material (Insulating body)	PA 6.6
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	17
Direction of rotation	Standard
Connection profile	17
Number (Contact group 1)	17
Contact diameter (Contact group 1)	1 mm
Litz wires Min. cross section (Contact group 1)	0.14 mm ²
Litz wires Max. cross section (Contact group 1)	0.56 mm ²
Rated current Contact (Contact group 1)	8 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Type	Cable connector housing
Thread type	M23
Type of locking	Screw locking mechanism
Pg screw connection	Pg16
Material (Housing)	GD-Zn
Material (Rotating parts)	CuZn
Material (Housing surface)	Ni
Material (Seal)	FPM (O-ring)

TGGM/CDIO/17-BU - Cable connector



1667905

<https://www.phoenixcontact.com/us/products/1667905>

Degree of protection (plugged in)	IP67
-----------------------------------	------


Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C (short-term up to 145°C)


Drawings

Schematic diagram



Connector pin assignment


Schematic diagram



Dimensional drawing

1667905

<https://www.phoenixcontact.com/us/products/1667905>



TGGM/CDIO/17-BU - Cable connector



1667905

<https://www.phoenixcontact.com/us/products/1667905>

Classifications

ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

ETIM

ETIM 10.0	EC002635
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1667905

<https://www.phoenixcontact.com/us/products/1667905>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ca0abb35-eaea-46ba-b53d-547abca79d59

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com