

# CK1,6-ED-1,00ST AU - Crimp contact



1674888

<https://www.phoenixcontact.com/us/products/1674888>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, series: HC-M-12, Pin, turned, contact diameter: 1.6 mm, connection cross section: 0.75 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 18...18, contact material: Cu alloy

## Commercial data

Item number	1674888
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF65
Product key	AF7AIA
GTIN	4017918135584
Weight per piece (including packing)	0.65 g
Weight per piece (excluding packing)	0.65 g
Customs tariff number	85366990
Country of origin	DE

# CK1,6-ED-1,00ST AU - Crimp contact



1674888

<https://www.phoenixcontact.com/us/products/1674888>

## Technical data

### Notes

General	for HC-M-12, HC-M-17, HC-M-03/04, HC-M-EMV, HC-D, HC-DD, HC-Q, and VC-D contact carriers
Assembly note	The quality of a crimp connection is determined by DIN EN 60352-2.
Assembly note	For voltages less than 5 V and currents less than 5 mA, gold-plated contacts are recommended.
Assembly note	<p>Note on crimp connection technology:</p> <p>For flexible wires only. The specified conductor cross-sections refer to the nominal cross-section of the cable used.</p> <p>The wiring space of the crimp connection technology is designed for fine-stranded cables in accordance with VDE 0295 Class 5. Deviating cable structures (e.g., Class 1.2 and 6 or AWG cables) should be checked before use.</p>

### Product properties

Product type	Crimp contact
Series	HC-M-12
	HC-M-EMV
	HC-D
	HC-DD
	VC-D
	HC-M-03/04
	HC-M-17
	HC-K
	HC-Q
	HC-COM
HC-M-42	
HC-M-08-MBIT	
Contact material type	turned

### Connection data

Connection technology	
Contact connection type	Pin
Connection method	Crimp connection
Conductor connection	
Stripping length	8 mm
Connection cross section (flexible)	0.75 mm <sup>2</sup> ... 1 mm <sup>2</sup>
Connection cross section	1 mm <sup>2</sup> ... 1 mm <sup>2</sup>
Connection cross section AWG	18 ... 18

### Material specifications

# CK1,6-ED-1,00ST AU - Crimp contact




1674888

<https://www.phoenixcontact.com/us/products/1674888>

Material Contact	Cu alloy
Material Contact surface	Au

## Dimensions

Dimensional drawing	
Diameter (Contact diameter)	1.6 mm

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

# CK1,6-ED-1,00ST AU - Crimp contact




1674888

<https://www.phoenixcontact.com/us/products/1674888>

## Drawings

Dimensional drawing



Dimensional drawing

# CK1,6-ED-1,00ST AU - Crimp contact



1674888

<https://www.phoenixcontact.com/us/products/1674888>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1674888>



**EAC**

Approval ID: RU C-DE.AI30.B.01102

# CK1,6-ED-1,00ST AU - Crimp contact



1674888

<https://www.phoenixcontact.com/us/products/1674888>

## Classifications

### ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

### ETIM

ETIM 10.0	EC000796
-----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

# CK1,6-ED-1,00ST AU - Crimp contact



1674888

<https://www.phoenixcontact.com/us/products/1674888>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)