

CK1,6-ED-0,37ST AU - Crimp contact



1674901

<https://www.phoenixcontact.com/us/products/1674901>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, series: HC-M-12, Pin, turned, contact diameter: 1.6 mm, connection cross section: 0.14 mm² ... 0.37 mm², AWG 26...22, contact material: Cu alloy

Commercial data

Item number	1674901
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BF65
Product key	AF7AIA
GTIN	4017918135607
Weight per piece (including packing)	0.714 g
Weight per piece (excluding packing)	0.685 g
Customs tariff number	85366990
Country of origin	DE

CK1,6-ED-0,37ST AU - Crimp contact



1674901

<https://www.phoenixcontact.com/us/products/1674901>

Technical data

Notes

General	for HC-M-12, HC-M-17, HC-M-03/04, HC-M-EMV, HC-D, HC-DD, HC-Q, and VC-D contact carriers
Assembly note	The quality of a crimp connection is determined by DIN EN 60352-2.
Assembly note	For voltages less than 5 V and currents less than 5 mA, gold-plated contacts are recommended.
Assembly note	<p>Note on crimp connection technology:</p> <p>For flexible wires only. The specified conductor cross-sections refer to the nominal cross-section of the cable used.</p> <p>The wiring space of the crimp connection technology is designed for fine-stranded cables in accordance with VDE 0295 Class 5. Deviating cable structures (e.g., Class 1.2 and 6 or AWG cables) should be checked before use.</p>

Product properties

Product type	Crimp contact
Series	HC-M-12 HC-M-EMV HC-D HC-DD VC-D HC-M-03/04 HC-M-17 HC-K HC-Q HC-COM HC-M-42 HC-M-08-MBIT
Contact material type	turned

Connection data

Connection technology	
Contact connection type	Pin
Connection method	Crimp connection
Conductor connection	
Stripping length	8 mm
Connection cross section	0.14 mm ² ... 0.37 mm ²
Connection cross section AWG	26 ... 22

Material specifications

Material Contact	Cu alloy
------------------	----------

CK1,6-ED-0,37ST AU - Crimp contact




1674901

<https://www.phoenixcontact.com/us/products/1674901>

Material Contact surface	Au
--------------------------	----

Dimensions

Dimensional drawing	
Diameter (Contact diameter)	1.6 mm

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CK1,6-ED-0,37ST AU - Crimp contact




1674901

<https://www.phoenixcontact.com/us/products/1674901>

Drawings

Dimensional drawing



Dimensional drawing

CK1,6-ED-0,37ST AU - Crimp contact



1674901

<https://www.phoenixcontact.com/us/products/1674901>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1674901>



EAC

Approval ID: RU C-DE.AI30.B.01102

CK1,6-ED-0,37ST AU - Crimp contact



1674901

<https://www.phoenixcontact.com/us/products/1674901>

Classifications

ECLASS

ECLASS-13.0	27440204
ECLASS-15.0	27440204

ETIM

ETIM 10.0	EC000796
-----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK1,6-ED-0,37ST AU - Crimp contact



1674901

<https://www.phoenixcontact.com/us/products/1674901>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.155 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com