

# SACB-8/ 8-L- 5,0PUR NPN - Distributor box



1680717

<https://www.phoenixcontact.com/us/products/1680717>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distributor box, connection method: M12 socket, number of slots: 8, number of positions: 4, status display: yes; master cable connection: Fixed connection, PUR/PVC, cable length: 5 m, shielding: no

## Commercial data

Item number	1680717
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	AF3CBA
GTIN	4017918169961
Weight per piece (including packing)	658.2 g
Weight per piece (excluding packing)	658.2 g
Customs tariff number	85444290
Country of origin	PL

# SACB-8/ 8-L- 5,0PUR NPN - Distributor box



1680717

<https://www.phoenixcontact.com/us/products/1680717>

## Technical data

### Product properties

Product type	Distributor box
Number of positions	4
Number of slots	8
LED	yes

### System properties

#### Local diagnostics

Monitored function	Supply voltage
Optical representation	Green LED

### Electrical properties

Max. operating voltage $U_{max}$	30 V DC
Local diagnostics	Supply voltage Green LED
	Status display I/O Yellow LED
Nominal voltage $U_N$	24 V DC
Rated current, total	12 A
Max. current carrying capacity per path	2 A
Current carrying capacity per slot	4 A

### Connection data

#### Conductor connection

Sensor/actuator connection system	M12 socket
Tightening torque slot sensor/actuator cable	0.4 Nm

### Signaling

Status display present	yes
------------------------	-----

### Material specifications

Material Housing	PA
Flammability rating according to UL 94	V0
Seal material O-ring	NBR
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA

### Cable/line


Cable length	5 m
--------------	-----

PUR/PVC black [PUR]

# SACB-8/ 8-L- 5,0PUR NPN - Distributor box

1680717

<https://www.phoenixcontact.com/us/products/1680717>

Dimensional drawing	
Cable weight	107.4 kg/km
UL AWM Style	20549 (80°C/300 V)
Number of positions	11
Shielded	no
Cable type	PUR/PVC black [PUR]
Conductor structure signal line	19x 0.15 mm
AWG signal line	22
Conductor structure, voltage supply	42x 0.15 mm
AWG power supply	18
Conductor cross-section	8x 0.34 mm <sup>2</sup> (Signal line) 3x 0.75 mm <sup>2</sup> (power line)
Wire diameter incl. insulation	1.3 mm ±0.1 mm (Signal line) 1.8 mm ±0.1 mm (power line)
External cable diameter	8.50 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, green/yellow, white, green, yellow, gray, pink, red, black, violet
Inner sheath thickness	≥ 0.15 mm
Thickness, outer sheath	≥ 0.38 mm
Overall twist	Wires twisted in layers
Max. conductor resistance	≤ 53 Ω/km (Signal line) ≤ 26 Ω/km (power line)
Insulation resistance	≥ 5 MΩ*km
Nominal voltage, cable	300 V AC
Test voltage Core/Core	2000 V (50 Hz, 5 min.)
Minimum bending radius, fixed installation	7.5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	64 mm
Smallest bending radius, movable installation	85 mm
Dynamic load capacity (bending)	Max. bending cycles: 1500000, Bending radius: 10 x D, Traversing path: 2 m, Traversing rate: 2 m/s
Flame resistance	DIN EN 50265
Resistance to oil	according to VDE 0472 Part 803

# SACB-8/ 8-L- 5,0PUR NPN - Distributor box



1680717

<https://www.phoenixcontact.com/us/products/1680717>

Other resistance	Highly resistant to acids, alkaline solutions and solvents
Special properties	Silicone-free
Ambient temperature (operation)	-40 °C ... 90 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67

# SACB-8/ 8-L- 5,0PUR NPN - Distributor box


1680717

<https://www.phoenixcontact.com/us/products/1680717>



## Drawings

Schematic diagram




M12 slot, socket, 4-pos.

# SACB-8/ 8-L- 5,0PUR NPN - Distributor box

1680717

<https://www.phoenixcontact.com/us/products/1680717>

Circuit diagram



# SACB-8/ 8-L- 5,0PUR NPN - Distributor box



1680717

<https://www.phoenixcontact.com/us/products/1680717>

## Classifications

### ECLASS

ECLASS-13.0	27440108
ECLASS-15.0	27440108

# SACB-8/ 8-L- 5,0PUR NPN - Distributor box



1680717

<https://www.phoenixcontact.com/us/products/1680717>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)