

# VS-BU-LK-3,6/22,8/4,6 - D-SUB power contact



1688272

<https://www.phoenixcontact.com/us/products/1688272>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power contacts, for D-SUB combination inserts, socket, solder cup, straight, rated current 40 A, gold-plated

## Commercial data

Item number	1688272
Packing unit	100 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAC
GTIN	4017918179670
Weight per piece (including packing)	1.927 g
Weight per piece (excluding packing)	1.9 g
Customs tariff number	85366990
Country of origin	DE

# VS-BU-LK-3,6/22,8/4,6 - D-SUB power contact



1688272

<https://www.phoenixcontact.com/us/products/1688272>

## Technical data

### Product properties

Product type	Contacts
Contact material type	turned

### Electrical properties

Rated current (Maximum load current)	40 A
Resistance (Insulation resistance)	$\geq 500 \text{ M}\Omega$

### Connection data

#### Connection technology

Contact connection type	Socket
Connection method	Solder cup

### Dimensions

Width [w]	5.5 mm
Height [h]	5.5 mm
Length [l]	23 mm
Diameter (Contact diameter)	4.6 mm

### Material specifications

Material Contact	Metal
------------------	-------

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	$\geq 500$
Insertion force	$\leq 7 \text{ N}$
Withdrawal force	approx. 5 N

### Characteristics

#### Measuring system

Resistance: Insulation resistance	$\geq 500 \text{ M}\Omega$
-----------------------------------	----------------------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-55 °C ... 130 °C
---------------------------------	-------------------

# VS-BU-LK-3,6/22,8/4,6 - D-SUB power contact



1688272

<https://www.phoenixcontact.com/us/products/1688272>

## Classifications

### ECLASS

ECLASS-13.0	27440392
ECLASS-15.0	27440392

### ETIM

ETIM 10.0	EC002943
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# VS-BU-LK-3,6/22,8/4,6 - D-SUB power contact



1688272

<https://www.phoenixcontact.com/us/products/1688272>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5aeb4754-03ac-4eac-bda8-15f3a063c171

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)