

# VS-15-ST-DSUB-CD-OG - D-SUB contact support



1688939

<https://www.phoenixcontact.com/us/products/1688939>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact carrier, shell size 2, for 15 signal contacts, type of contact pin, for crimp contacts, straight, fixing with a 3 mm hole, for panel mounting frame and sleeve housing VS-15-...



## Your advantages

- D-SUB 15 connection
- Compatible with IP67 sleeve housing and panel-mount frame
- Easy assembly

## Commercial data

Item number	1688939
Packing unit	100 pc
Minimum order quantity	1 pc
Sales key	AB19
Product key	ABNCAA
GTIN	4017918823085
Weight per piece (including packing)	7.306 g
Weight per piece (excluding packing)	6.29 g
Customs tariff number	85366990
Country of origin	DE

1688939

<https://www.phoenixcontact.com/us/products/1688939>

## Technical data

### Product properties

Product type	Contact insert
Type	D-SUB
Number of positions	15
Connection profile	D-SUB 15
Shielded	no

### Insulation characteristics

Overvoltage category	III
Degree of pollution	2

### Electrical properties

Rated voltage in acc. with IEC 61076-2-101	400 V
Rated voltage (III/3)	125 V
Rated surge voltage	1 kV
Rated current	5 A (at 20 °C)
Test voltage	1200 V
Transmission medium	Copper

### Connection data

Connection method	Crimp connection
-------------------	------------------

### Dimensions

Width	18 mm
Height	12.93 mm
Length	39.52 mm

### Material specifications

Flammability rating according to UL 94	V0
Housing material	Steel, tin-plated
Contact material	Copper alloy
Contact carrier material	Glass-fiber reinforced thermoplastics, UL 94 V0

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	≥ 500
Insertion force per signal contact	≤ 3.40 N

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-55 °C ... 130 °C
---------------------------------	-------------------

# VS-15-ST-DSUB-CD-OG - D-SUB contact support



1688939

<https://www.phoenixcontact.com/us/products/1688939>

## Mounting

Mounting type	Hole
---------------	------

# VS-15-ST-DSUB-CD-OG - D-SUB contact support



1688939

<https://www.phoenixcontact.com/us/products/1688939>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1688939>



**UL Recognized**

Approval ID: E118976

1688939

<https://www.phoenixcontact.com/us/products/1688939>

## Classifications

### ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

### ETIM

ETIM 10.0	EC001132
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1688939

<https://www.phoenixcontact.com/us/products/1688939>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)